

Distributed by:





**[www.Jameco.com](http://www.Jameco.com) ♦ 1-800-831-4242**

The content and copyrights of the attached  
material are the property of its owner.


Jameco Part Number 116012

# 1007 Series



## D-SUB I.D.C. Type




(ROHS)



Without Insulator Support



With Insulator Support



Strain Relief

### Dimensions

| Positions | A     | B     | C     | D     | E     | F     |
|-----------|-------|-------|-------|-------|-------|-------|
| 9         | 30.81 | 24.99 | 16.92 | 16.33 | 11.08 | 10.16 |
| 15        | 39.14 | 33.32 | 25.50 | 24.66 | 19.39 | 17.78 |
| 25        | 53.04 | 47.04 | 38.96 | 38.38 | 33.24 | 30.48 |
| 37        | 69.32 | 63.50 | 55.42 | 54.84 | 49.86 | 45.72 |