

- FAQ's
- Product Bulletins
- PDFObsolete and ..
- Selection Guides
- PDFConvenience ..

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

- Insulation support helps to prevent wire damage in bending applications
 - Ring tongue design assures a secure connection in high vibration applications
 - Brazed seam protects terminal barrel from splitting during the crimp process
 - Internal barrel serrations assure good wire contact and maximum tensile strength
 - UL Flammability UL 94V-0, maximum insulation temperature 221°F (105°C)
 - UL and CSA rated up 600 V per UL 486A/B, where applicable
- ‡UL and CSA approved tooling/product combinations.
- Note: Wire sizes #26 – #22 AWG, are not UL Listed or CSA Certified.