

High Speed Standard Edge Connector (Continued)

Dimensions									No. of Dual Positions	Part Number
A	B	C	D	E	F	G	H	J		
79.15 3.116	33.40-33.66 1.315-1.325	40.77-41.02 1.605-1.615	33.71-33.66 1.327-1.333	41.07-41.22 1.617-1.623	21	27	4.44-4.95 .175-.195	2.29-2.79 .090-.110	50	145090-1
								2.92-3.43 .115-.135	50	145090-2
91.85 3.616	38.48-38.74 1.515-1.525	48.39-48.64 1.905-1.915	38.79-38.94 1.527-1.533	46.69-48.84 1.917-1.923	25	33	4.44-4.95 .175-.195	2.29-2.79 .090-.110	60	145090-5
								2.92-3.43 .115-.135	60	145090-6
								4.57-5.08 .180-.200	60	145090-8
104.55 4.116	43.56-43.82 1.715-1.725	55.01-56.26 2.205-2.215	43.87-44.02 1.727-1.733	56.31-56.46 2.217-2.223	29	39	4.44-4.95 .175-.195	2.29-2.79 .090-.110	70	145090-9
								2.92-3.43 .115-.135	70	1-145090-0
117.25 4.616	51.18-51.44 2.015-2.025	61.09-61.34 2.405-2.415	51.49-51.64 2.027-2.033	61.39-61.54 2.417-2.423	35	43	4.44-4.95 .175-.195	2.29-2.79 .090-.110	80	1-145090-3
								2.92-3.43 .115-.135	80	1-145090-4
129.95 5.116	56.26-56.52 2.215-2.225	68.71-68.96 2.705-2.715	56.57-56.72 2.227-2.233	69.01-69.16 2.717-2.723	39	49	4.44-4.95 .175-.195	2.29-2.79 .090-.110	90	1-145090-7
								2.92-3.43 .115-.135	90	1-145090-8
								3.68-4.19 .145-.165	90	1-145090-9
142.65 5.616	61.34-61.60 2.415-2.425	76.33-76.58 3.005-3.015	61.65-61.80 2.427-2.433	76.63-76.78 3.017-3.023	43	55	4.44-4.95 .175-.195	2.29-2.79 .090-.110	100	2-145090-1
								2.92-3.43 .115-.135	100	2-145090-2
155.35 6.116	66.42-66.68 2.615-2.625	83.95-84.20 3.305-3.315	66.73-66.88 2.627-2.633	84.25-84.40 3.317-3.323	47	61	4.44-4.95 .175-.195	2.29-2.79 .090-.110	110	2-145090-5
								2.92-3.43 .115-.135	110	2-145090-6
								3.68-4.19 .145-.165	110	2-145090-7
								4.57-5.08 .180-.200	110	2-145090-8
168.05 6.616	71.50-71.76 2.815-2.825	91.57-91.82 3.605-3.615	71.81-71.96 2.827-2.833	91.87-92.02 3.617-3.623	51	67	4.44-4.95 .175-.195	2.29-2.79 .090-.110	120	2-145090-9
								2.92-3.43 .115-.135	120	3-145090-0
								3.68-4.19 .145-.165	120	3-145090-1
180.75 7.116	79.12-79.38 3.115-3.125	96.65-96.90 3.805-3.815	79.43-79.58 3.127-3.133	96.95-97.10 3.817-3.823	57	71	4.44-4.95 .175-.195	2.29-2.79 .090-.110	130	3-145090-3
								2.92-3.43 .115-.135	130	3-145090-4
								3.68-4.19 .145-.165	130	3-145090-5
108.36 4.266	46.10-46.36 1.815-1.825	57.28-57.53 2.255-2.265	46.41-46.56 1.827-1.833	57.58-57.73 2.267-2.273	31	40	4.44-4.95 .175-.195	2.29-2.79 .090-.110	73	3-145090-7*
								2.92-3.43 .115-.135	73	3-145090-8*

*Alternate Pattern Applies.

5

High Speed Card Edge Products