



COASTTM
LIGHTS • KNIVES • MULTI-TOOLS

2012

PRODUCTS

Introduction	4–5
--------------------	-----

LED HANDHELDS

Technology	6–10
High Performance LED Lights	11–13
Professional Use LED Lights	14–15
Tactical Use LED Lights	16
General Use LED Lights	17–20
A-Series LED Lights.....	21–22

HEADLAMPS

Technology	23–25
LED Headlamps	26–27

EMERGENCY AREA LIGHTS

Technology	28–29
EALs	30–31

KNIVES

Technology	32–35
Rapid Response®	36
Double-Lock™ Knives.....	37–39
Liner-Lock® and Lockback Knives	40–44
LED Knives.....	45–46
Fixed Blade Knives	47
Swiss Army Style Knives.....	48
Fishing Knives & Tools	49–51

MULTI-TOOLS

Technology	52
Multi-Tools.....	53–55

ACCESSORIES

Knife & Tool Sharpeners.....	56
------------------------------	----

DISPLAYS

Product Displays	57–60
------------------------	-------

SPECS CHART

LED Lights Specifications	61–63
Knives & Tools Specifications.....	64–66

COAST™

LIGHTS • KNIVES • MULTI-TOOLS

COAST Products is a 93-year-old, family-owned company that produces LED lights, knives, and multi-tools for work, recreation, and everyday use.

COAST produces innovative, technologically advanced products backed by a lifetime guarantee that makes the user's life safer, easier, and more enjoyable.



LIFETIME GUARANTEE: COAST Products guarantees this product to be free of defects in materials and workmanship for the life of the original purchaser. This guarantee does not cover normal wear and tear, nor damage resulting from misuse or neglect. If this product is defective, return it to us for repair or replacement, along with a check for \$5.00 shipping and handling. Guarantee does not include batteries.

A handwritten signature in black ink, which appears to read 'David C. Brands'.

David C. Brands—Owner, COAST Products

Quality in Action




I am currently stationed in Iraq at Joint Base Balad. I purchased one of your LED flashlights...and it has been an invaluable asset to me getting the job I do here done. Thank you for having such wonderful products for us in the military available for us to purchase here.

—Steven P.


Since 1995, COAST has provided over 500,000 lights, knives, and multi-tools to U.S. military installations all over the world.



LED Handheld Technology



Pure Beam™ Focusing Optic System



FLOOD BEAM



- Larger light area
- Superior beam consistency

BULLS-EYE SPOT™ BEAM



- Longer beam distance
- More intense Bulls-Eye Spot™ Beam
- More consistent halo
- More light area

Max-Beam™ Fixed Optic Technology

The Maximum
Amount of
Light for Your
Application

FLOOD BEAM

for
General Use



BULLS-EYE SPOT™ BEAM

for
Tactical &
Professional Use



INSPECTION BEAM

for
Up-Close &
Inspection
Use



Key Technologies



Fingertip Speed Focus Control™ & Beam Lock™

Many of our High Performance lights feature a one-handed system for moving from a broad flood beam to a focused spot beam. A simple push forward or pull back with the thumb on the head of the light adjusts the beam to suit your application. Then simply twist to lock in exactly the beam you need.



Twist Focus System

Twist the head of the flashlight to move between a flood and a spot beam.



Quick-Cycle Switch System™

To activate the high-output setting from the OFF position, fully depress and release the switch one time. High output setting is the standard setting when a bright light is needed. To activate the 50% beam setting from the OFF position, fully depress and release the switch two times. 50% output is useful for reading, report writing, identification and personal inspections.


Some COAST lights also feature a strobe as the second part of the cycle. In this case, the light sequence is high, strobe, low.



Dual Color

COAST dual color lights have both clear, bright white LEDs and a red LED. The white LEDs are perfect for general use, while the red LED offers glare-free light. Because the red beam doesn't cause the pupils of the eye to constrict, it preserves night vision. This makes it useful for reading maps at night or for locating things outdoors or in a darkened room without the dazzling glare of a white light.

Glossary of LED Flashlight Icons

 Fingertip Speed Focus™ Beam Lock™	FINGERTIP SPEED FOCUS – BEAM LOCK™: Focusing system that allows you to adjust your light from flood to spot with just your fingertip. Lock the beam focus in any position you want.
 4 Colors 4 Power Switches	4 COLORS, 4 POWER SWITCHES: Our 4-color system combines one white LED, one red LED, one blue LED, one green LED, each color controlled with its own switch.
 MAX BEAM™ OPTIC Bulls-Eye Spot™	MAX BEAM™ OPTIC – BULLS-EYE SPOT™: It produces our Bulls-Eye Spot™ beam giving you a great focused spot, while producing an outer ring of flood light which allows you to see a broader area for added side vision.
 MAX BEAM™ OPTIC White Flood Beam	MAX-BEAM™ OPTIC – WHITE FLOOD BEAM: Multiple LEDs project a wide, flood beam giving you the maximum amount of light with no dark spots.
 MAX BEAM™ OPTIC White Inspection Beam	MAX-BEAM™ OPTIC – WHITE INSPECTION BEAM: Produces a tight inspection beam, giving you the most useful light beam for short distance applications.
 PURE BEAM™ FOCUSING OPTIC Flood Beam / Bulls-Eye Spot™	PURE BEAM™ FOCUSING OPTIC – FLOOD BEAM / BULLS-EYE SPOT™: Our patented focusing system that provides superior beam consistency from spot to flood, with no dark rings typically associated with focusing flashlights.
 QUICK-CYCLE SWITCH™ High & Low	QUICK-CYCLE SWITCH – HIGH & LOW: Allows you to select between a high output or a low output setting so you can choose the right level for your application.
 QUICK-CYCLE SWITCH™ High / Strobe / Low	QUICK-CYCLE SWITCH – HIGH, STROBE & LOW: Allows you to select between a high output, strobe, or low output setting so you can choose the right level for your application.
 Twist to Focus	TWIST TO FOCUS: Our twist focusing system
 White Flood & Red Spot Beam	WHITE FLOOD AND RED SPOT BEAM: Our dual-color system combines five white LEDs with one red LED, each color controlled with its own switch.
 White Flood & UV Spot Beam	WHITE FLOOD AND UV SPOT BEAM: Our dual-color system combines three white LEDs with three UV LEDs, each color controlled with its own switch.

HP21R


Box Item# 19390



- 15.50 in. length
- Ni-MH batteries (included)

Includes:

- Carrying case
- AC charger
- DC charger
- Shoulder strap



HP21



Box Item# 19282



- 15.50 in. length
- 4 D batteries (included)

Includes:

- Carrying case
- Shoulder strap






HP17

Clam Pack Item# HP8417CP



- 13.12 in. length
- 3 D batteries (included)




HP14

Clam Pack Item# HP8414CP

Box Item# 19280



- 8.38 in. length
- 4 AA batteries (included)



HP7 Titanium


Clam Pack Item# HP8420-TCP-P3

Box Item# 19235


HP7 Black

Clam Pack Item# HP8407CP

Box Item# 19279




- 5.58 in. length
- 4 AAA batteries (included)




HP6

Clam Pack Item# HP8406CP

Box Item# 19278




- 6.62 in. length
- 2 AA batteries (included)




HP5

Clam Pack Item# HP8405CP

Box Item# 19277




- 4.65 in. length
- 1 AA battery (included)



HP4

Clam Pack Item# HP8404CP

Box Item# 19276



- 5.54 in. length
- 2 AAA batteries (included)



HP17TAC



Box Item# 19281



FL1 STANDARD			
615 LUMENS	269m	15h 15min	1m
LIGHT OUTPUT	BEAM DISTANCE	RUNTIME	IMPACT RESISTANCE



- 13.12 in. length
- 3 D batteries (included)



HP7TAC


Clam Pack Item#
HP8407AFCP



FL1 STANDARD			
251 LUMENS	196m	5h 45min	1m
LIGHT OUTPUT	BEAM DISTANCE	RUNTIME	IMPACT RESISTANCE



- 5.58 in. length
- 4 AAA batteries (included)



HP6TAC


Clam Pack Item#
HP8406AFCP



FL1 STANDARD			
170 LUMENS	104m	5h	1m
LIGHT OUTPUT	BEAM DISTANCE	RUNTIME	IMPACT RESISTANCE



- 6.62 in. length
- 2 AA batteries (included)



HP5TAC


Clam Pack Item#
HP8405AFCP



FL1 STANDARD			
121 LUMENS	78m	4h 30min	1m
LIGHT OUTPUT	BEAM DISTANCE	RUNTIME	IMPACT RESISTANCE



- 4.65 in. length
- 1 AA battery (included)



PX50

Clam Pack Item# TT7456CP



FL1 STANDARD			
131 LUMENS	195m	9h 15min	1m
LIGHT OUTPUT	BEAM DISTANCE	RUNTIME	IMPACT RESISTANCE

- Waterproof
- 6.50 in. length
- 4 AA batteries (included)



PX45


Clam Pack Item# 19285

Box Item# 19265



FL1 STANDARD			
212 LUMENS	186m	7h 15min	1m
LIGHT OUTPUT	BEAM DISTANCE	RUNTIME	IMPACT RESISTANCE

- 5.20 in. length
- 3 AAA batteries (included)



PX25


Clam Pack Item# TT7736CP

Box Item# 19270



FL1 STANDARD			
208 LUMENS	128m	6h 15min	1m
LIGHT OUTPUT	BEAM DISTANCE	RUNTIME	IMPACT RESISTANCE


- 4.70 in. length
- 3 AAA batteries (included)



PX20 Dual Color (red/white)

Clam Pack Item# 19286


Box Item# 19271



- 3.95 in. length
- 3 AAA batteries (included)




White Flood & Red Spot Beam




Red Beam
preserves night vision

PX10 Dual Color (UV/white)


Box Item# 19269



- 3.95 in. length
- 3 AAA batteries (included)



White Flood & UV Spot Beam




UV beam for inspection


PX5

Clam Pack Item# HP8313CP

Box Item# 19275



- 2.75 in. length
- 4 AG13 batteries (included)



Flood Beam / Bulls-Eye Spot™

TX40

Clam Pack Item# TT7736TSCP

Box Item# 19272




- 5.94 in. length
- 3 AAA batteries (included)
- Optional Pressure Switch makes the TX40 the ideal weapon-mounted light.

TX10 Quad Color

Clam Pack Item# TT77364CP

White, red, blue, green light beams



- 3.95 in. length
- 3 AAA batteries (included)
- White—flood beam
- Red—preserves night vision
- Green—night map reading
- Blue—track blood when hunting


G50

Clam Pack Item# TT8607CP
Box Item# 19299



FL1 STANDARD			
166 LUMENS	143m	7h	1m
LIGHT OUTPUT	BEAM DISTANCE	RUNTIME	IMPACT RESISTANCE

- 4.80 in. length
- 3 AAA batteries (included)



G45 Black

Clam Pack Item# 19300
Box Item# 19356

G45 Titanium

Clam Pack Item# TT7345SCP



FL1 STANDARD			
135 LUMENS	53m	8h 30min	1m
LIGHT OUTPUT	BEAM DISTANCE	RUNTIME	IMPACT RESISTANCE

- 4.60 in. length
- 3 AAA batteries (included)




G30

Clam Pack Item# TT8606CP
Box Item# 19298




FL1 STANDARD			
121 LUMENS	146m	2h	1m
LIGHT OUTPUT	BEAM DISTANCE	RUNTIME	IMPACT RESISTANCE

- 6.46 in. length
- 2 AA batteries (included)



G40

Clam Pack Item# TT1006CP




- 6.03 in. length
- 3 AAA batteries (included)




G35 Dual Color

Clam Pack Item# TT1106CP



- 6.03 in. length
- 3 AAA batteries (included)




G25 Black


Clam Pack Item# TT7547BLCP
Box Item# 19355

G25 Titanium

Clam Pack Item# TT7547CP




- 6.05 in. length
- 2 AA batteries (included)



G20

Clam Pack Item# TT7817CP

Box Item# 19304



- 5.65 in. length
- 2 AAA batteries (included)



G19

Clam Pack Item# 19384




- 4.02 in. length
- 1 AAA battery (included)



G15

Clam Pack Item# TT75331CP



- 3.70 in. length
- 1 AAA battery (included)




G10 Black

Clam Pack Item# TT7830CP

G10 Titanium

Clam Pack Item# TT7831CP



- 3.70 in. length
- 1 AAA battery (included)

G5

Clam Pack Item# TT7839CP



G5

6-Pack (2 black, 2 red, & 2 titanium) Item# C07002CP



- 2.45 in. length
- 4 AG5 batteries (included)


A25

Box Item# 19247



FL1 STANDARD			
226 LUMENS	205m	5h	1m
LIGHT OUTPUT	BEAM DISTANCE	RUNTIME	IMPACT RESISTANCE

- 5.50 in. length
- 4 AAA batteries (included)
- Stainless steel body



A20

Box Item# 19267



FL1 STANDARD			
171 LUMENS	64m	6h 15min	1m
LIGHT OUTPUT	BEAM DISTANCE	RUNTIME	IMPACT RESISTANCE

- 3.67 in. length
- 3 AAA batteries (included)
- Heavy-duty sheath included
- Stainless steel body



A15

Box Item# 19266



FL1 STANDARD			
194 LUMENS	127m	3h 45min	1m
LIGHT OUTPUT	BEAM DISTANCE	RUNTIME	IMPACT RESISTANCE

- 3.90 in. length
- 3 AAA batteries (included)
- Heavy-duty sheath included
- Stainless steel body



A10

Box Item# 19246



- 5.48 in. length
- 2 AAA batteries (included)
- Includes stainless steel pocket clip
- Stainless steel body



A9

Clam Pack Item# 19364

Box Item# 19335





- 7.03 in. length
- 3 AAAA batteries (included)
- Includes stainless steel pocket clip
- Stainless steel body



A5

Box Item# 19245



- 3.74 in. length
- 1 AAA battery (included)
- Includes stainless steel pocket clip
- Stainless steel body





LED Headlamp Technology



Glossary of Headlamp Icons

 Hinged beam adjustment	HINGED BEAM ADJUSTMENT: Allows you to adjust direction of light beam.
 Bulls-Eye Spot™	MAX BEAM™ OPTIC – BULLS-EYE SPOT™: It produces our Bulls-Eye Spot™ beam giving you a great focused spot, while producing an outer ring of flood light which allows you to see a broader area for added side vision.
 White Flood Beam	MAX-BEAM™ OPTIC – WHITE FLOOD BEAM: Multiple LEDs project a wide, flood beam giving you the maximum amount of light with no dark spots.
 Flood Beam / Bulls-Eye Spot™	PURE BEAM™ FOCUSING OPTIC – FLOOD BEAM / BULLS-EYE SPOT™: Our patented focusing system that provides superior beam consistency from spot to flood, with no dark rings typically associated with focusing flashlights.
 Dimming function controls light output	VARIABLE LIGHT TECHNOLOGY: Dimming function that allows you to adjust your light output to just the right level for your application.
 White Flood & Red Spot Beam	WHITE FLOOD AND RED SPOT BEAM: Our dual-color system combines five white LEDs with one red LED, each color controlled with its own switch.

HL7R Rechargeable

Clam Pack Item# TT7498CP



Box Item# 19274*

(*Box item includes hardhat clips)

FL1 STANDARD			
 150 LUMENS	 114m	 3h	 1m
LIGHT OUTPUT	BEAM DISTANCE	RUNTIME	IMPACT RESISTANCE



- Z cord in headband
- 3 Ni-MH rechargeable batteries (included)
- AC recharger (included)
- Neoprene pouch included



HL7

Clam Pack Item# 19284



Box Item# 19273*

(*Box item includes hardhat clip)

FL1 STANDARD			
 196 LUMENS	 109m	 5h 45min	 1m
LIGHT OUTPUT	BEAM DISTANCE	RUNTIME	IMPACT RESISTANCE



- Z cord in headband
- 3 AAA batteries (included)
- Neoprene pouch included



HL6

Clam Pack Item# TT7468CP


Box Item# 19268*

(*Box item includes hardhat clip)

FL1 STANDARD			
 181 LUMENS	 111m	 6h 15min	 1m
LIGHT OUTPUT	BEAM DISTANCE	RUNTIME	IMPACT RESISTANCE



- Z cord in headband
- 3 AAA batteries (included)
- Neoprene pouch included




HL5

Clam Pack Item# TT7041CP
Box Item# 19351

FL1 STANDARD			
 175 LUMENS LIGHT OUTPUT	 56m BEAM DISTANCE	 3h 45min RUNTIME	 1m IMPACT RESISTANCE



- 3 AAA batteries (included)




HL4 Dual Color (red/white)

Clam Pack Item# 19291

FL1 STANDARD			
 144 LUMENS LIGHT OUTPUT	 57m BEAM DISTANCE	 6h 15min RUNTIME	 1m IMPACT RESISTANCE



- 3 AAA batteries (included)




HL3

Clam Pack Item# TT7454CP
Box Item# 19350

FL1 STANDARD			
 60 LUMENS LIGHT OUTPUT	 43m BEAM DISTANCE	 12h 30min RUNTIME	 1m IMPACT RESISTANCE



- 3 AAA batteries (included)





LED Emergency Area Light Technology

COAST LIGHT DIAL™

Lets You Choose the Right Light for Every Situation



Energy Saving

- Adjusts to any light level
- The lower the light, the longer the battery life
- Area lighting, night lighting



Solid Red

- Signal light
- Maintains night vision
- Most energy efficient




Area Light

- Full power
- Most light output
- Up to 375 lumens



Flashing Red

- Emergency
- Warning
- Signal



Built-in Battery Life Indicator

Green	100–60%
Orange	60–30%
Red	30–0%

EAL20

Box Item# CE7124HGB



- 8.25 in. height
- Uses 4 D batteries (not included)

COAST Light Dial™ lets you choose the right light for every situation with VLT Dimming Technology & 4 light modes

Battery Life Indicator

Up to
375
LUMENS
Light Output

100
HOURS
ENERGY MODE
One set
of Batteries



Flashing Red



Solid Red



Area Light



Energy Saving

EAL15

Clam Pack Item# C7050CP



COAST Smart Switch 5-light-mode control

- 7.50 in. height
- Uses 4 C batteries (not included)
- 3 levels of white light (high/medium/low)
- 2 red modes (solid/flashing)

Up to
60
LUMENS
Light Output

50
HOURS
ENERGY MODE
One set
of Batteries



Flashing Red



Area Light



Solid Red



Energy Saving

EAL10

Clam Pack Item# C7040CP



COAST Smart Switch
4-light-mode control

- 5.75 in. length
- Uses 4 AA batteries (not included)
- 2 levels of white light (high/low)
- 2 red modes (solid/flashing)



Up to
17
LUMENS
Light Output

30
HOURS
ENERGY MODE
One set
of Batteries



Flashing Red



Area Light



Solid Red



Energy Saving

EAL5

Clam Pack Item# C7044CP



COAST Smart Switch
3-light-mode control

- 5.375 in. length
- Uses 4 AAA batteries (not included)



Up to
15
LUMENS
Light Output


40
HOURS
ENERGY MODE
One set
of Batteries



Handheld
Flashlight



Solid
White




Emergency Red:
Constant and Flashing



Introducing COAST's New Patented Blade-Assist Line of Knives

Rapid Response® Knives

Advanced Knife Technology



S.A.T.™
SMOOTH ASSIST
TECHNOLOGY

Smooth Assist Technology— Not Just FASTER...SMOOTHER

Our patented system not only assists the blade to open quickly but smoothly due to its *friction-reducing roller-bearing* design. When the spring moves the blade out of the handle, it rides on the roller bearing, allowing the blade to open smoothly and quickly—without requiring tremendous spring force. The roller bearing also reduces the spring load on all internal blade-assist components for a lifetime of reliable, smooth, and fast operation.



MAX-LOCK™

Max-Lock™ Technology

Conveniently positioned on the side of the handle allowing easy access for your thumb to lock or unlock the safety. Move it forward to lock and back to unlock. This secondary lock can be engaged with the blade open *or* closed.

Double-Lock™ Technology



Knife shown is Dark Force II,
our 19357 located on page 39.



Double-Lock™ System

DOUBLE-LOCK™

Look for our new Double-Lock™ technology in our large Liner-Lock® knives. When pushed forward into its engaged position, it prevents the Liner-Lock® from moving out of its locked position.

Also included is a *tension-adjusting feature* so the user can adjust the detent force required to move the Double-Lock™ forward to engagement and rearward to the off position.

The Double-Lock™ system works well for any knife owner and when it is engaged, adds that extra margin of safety for those that use their knife in extremely rugged conditions. For fire & rescue, police, military or challenging situations faced by anyone, the Double-Lock™ sets the new standard for extreme use, knife safety, and convenience.

Glossary of Knife Icons

 S.A.T.™ SMOOTH ASSIST TECHNOLOGY	S.A.T.™ SMOOTH ASSIST TECHNOLOGY: S.A.T.™ uses its friction-reducing roller-bearing design to allow the blade to open quickly but smoothly while reducing spring load on all internal blade-assist components. When the spring moves the blade out of the handle, it rides on the roller bearing, allowing the blade to open smoothly and quickly—without requiring tremendous spring force.
 MAX-LOCK™	MAX-LOCK™: The Max-Lock™ is a safety button on the side of the knife's handle that can lock the blade in both the open and closed positions.
 DOUBLE-LOCK™	DOUBLE-LOCK™: The Double-Lock™ safety switch mechanism works in conjunction with a primary Liner-Lock® blade lock system to prevent its disengagement. This makes a Liner-Lock® doubly safe.
 LINER-LOCK®	LINER-LOCK®: The Liner-Lock® locking mechanism is a portion of the blades handle-liner that moves from the side of the handle into position to block the blade from closing when the blade is opened. This steel portion of the liner must be pushed to the side before the blade can be closed.
 LOCKBACK	LOCKBACK: The Lockback blade locking system is located in the top of the knife handle and locks the blade by dropping a locking-bar into a locking notch at the top back-end of the blade.
 MIDLOCK	MIDLOCK: The Midlock blade locking system is located in the top of the knife handle and locks the blade by dropping into a locking notch at the top back-end of the blade. The lock release is located midpoint between the front and back of the handle.
 FRAME-LOCK	FRAME-LOCK: The Frame-Lock blade locking mechanism is part of the knife's frame that moves from the side frame of the knife when the blade is opened to block the blade from closing. This steel component of the frame must be pushed to the side to allow the blade to close.
 BUTTON-LOCK	BUTTON-LOCK: The Button-Lock is a Liner-Lock® release button located in the side of the knife's handle and when it is pushed it releases the Liner-Lock® mechanism allowing the blade to close.

Rapid Response® 3.00

Clam Pack Item# 19211

Box Item# 19391



MAX-LOCK™



S.A.T.™
SMOOTH ASSIST
TECHNOLOGY

- Blade length: 3.00 in.
- Overall length open: 7.00 in.
- Weight: 3.70 oz.
- Blade material: High-carbon stainless steel
- Handle material: Fiberglass-filled textured nylon

Rapid Response® 3.00 Black

Clam Pack Item# 19212

Box Item# 19392



MAX-LOCK™



S.A.T.™
SMOOTH ASSIST
TECHNOLOGY

Black oxide coated

- Blade length: 3.00 in.
- Overall length open: 7.00 in.
- Weight: 3.70 oz.
- Blade material: High-carbon stainless steel
- Handle material: Fiberglass-filled textured nylon

Rapid Response® 3.90

Clam Pack Item# 19213

Box Item# 19393



MAX-LOCK™



S.A.T.™
SMOOTH ASSIST
TECHNOLOGY

- Blade length: 3.90 in.
- Overall length open: 8.75 in.
- Weight: 4.80 oz.
- Blade material: High-carbon stainless steel
- Handle material: Fiberglass-filled textured nylon

Rapid Response® 3.90 Black

Clam Pack Item# 19214

Box Item# 19394



MAX-LOCK™



S.A.T.™
SMOOTH ASSIST
TECHNOLOGY

Black oxide coated

- Blade length: 3.90 in.
- Overall length open: 8.75 in.
- Weight: 4.80 oz.
- Blade material: High-carbon stainless steel
- Handle material: Fiberglass-filled textured nylon

Black Magic Liner-Lock®

Clam Pack Item# CG006CP

Box Item# CG006



DOUBLE-LOCKTM

- Liner-Lock® with Double-LockTM safety
- Blade material: 7Cr17 stainless steel
- Handle material: Checkered aluminum
- Stainless steel fasteners
- Blade length: 3.35 in.
- Length closed: 4.50 in.
- Overall length open: 7.75 in.
- Weight: 3.20 oz.

Ghost I

Clam Pack Item# 19311

Box Item# 19312



DOUBLE-LOCKTM

- Liner-Lock® with Double-LockTM safety
- Blade material: 7Cr17 stainless steel
- Grip-enhanced aluminum frame with stainless steel Double-LockTM Liner-Lock®
- Drop-point blade with false edge
- Stainless steel fasteners
- Deep-carry pocket clip
- Blade length: 3.25 in.
- Length closed: 4.65 in.
- Overall length open: 7.87 in.
- Weight: 3.80 oz.

Ghost II

Clam Pack Item# 19313

Box Item# 19314



DOUBLE-LOCKTM

- Blade material: 7Cr17 stainless steel
- Handle material: Grip-enhanced aluminum frame with stainless steel Double-LockTM Liner-Lock®
- Drop-point blade with thumb perch
- Stainless steel fasteners
- Deep-carry pocket clip
- Blade length: 3.50 in.
- Length closed: 4.65 in.
- Overall length open: 8.00 in.
- Weight: 3.90 oz.

P.D.T. Police Duty Tactical

Clam Pack Item# 19305

Box Item# 19306



DOUBLE-LOCK™

- Blade material: 7Cr17 stainless steel
- Handle material: Grip-enhanced aluminum frame with stainless steel Double-Lock™ Liner-Lock®
- One-inch serrated blade segment
- Stainless steel fasteners
- Deep-carry 3-position pocket clip
- Blade length: 3.25 in.
- Length closed: 4.70 in.
- Overall length open: 8.12 in.
- Weight: 4.20 oz.

R.T.O.-I Rescue Team Operator

Clam Pack Item# 19307

Box Item# 19308



DOUBLE-LOCK™

- Blade material: 7Cr17 stainless steel
- Handle material: Grip-textured aluminum frame with stainless steel Double-Lock™ Liner-Lock®
- One-inch serrated blade segment
- Seat belt cutter & glass breaker
- Deep-carry pocket clip
- Blade length: 3.25 in.
- Length closed: 4.87 in.
- Overall length open: 8.12 in.
- Weight: 4.20 oz.

R.T.O.-II Rescue Team Operator

Clam Pack Item# 19309

Box Item# 19310



DOUBLE-LOCK™

- Blade material: 7Cr17 stainless steel
- Handle material: Grip-textured aluminum frame with stainless steel Double-Lock™ Liner-Lock®
- Clothing removal/seat belt blade serration
- Seat belt cutter & glass breaker
- Deep-carry pocket clip
- Blade length: 3.25 in.
- Length closed: 4.87 in.
- Overall length open: 8.12 in.
- Weight: 4.20 oz.

Tactical Liner-Lock®

Clam Pack Item# C19CP

Box Item# C19



DOUBLE-LOCK™

- Blade material: 7Cr17 stainless steel
- Handle material: Black aluminum frame with stainless steel Double-Lock™ Liner-Lock®
- Ambidextrous thumb stud
- Stainless steel fasteners
- Deep-carry stainless steel pocket clip
- Blade length: 3.35 in.
- Length closed: 4.65 in.
- Overall length open: 8.00 in.
- Weight: 3.50 oz.

Dark Force I

Clam Pack Item# 19339

Box Item# 19340



DOUBLE-LOCK™

- Blade material: 7Cr17 stainless steel
- Handle material: G-10 with stainless steel frame & Double-Lock™ Liner-Lock®
- Drop-point blade with thumb perch
- Stainless steel fasteners
- Ambidextrous thumb-stud
- Deep-carry 3-position pocket clip
- Blade length: 3.50 in.
- Length closed: 4.75 in.
- Overall length open: 8.25 in.
- Weight: 5.00 oz.

Dark Force II

Clam Pack Item# 19357

Box Item# 19358



DOUBLE-LOCK™

- Blade material: 7Cr17 stainless steel
- Handle material: G-10 with stainless steel frame & Double-Lock™ Liner-Lock®
- Drop-point blade with thumb perch
- One-inch serrated blade segment
- Stainless steel fasteners
- Ambidextrous thumb-stud
- Deep-carry 3-position pocket clip
- Blade length: 3.50 in.
- Length closed: 4.75 in.
- Overall length open: 8.25 in.
- Weight: 5.00 oz.

Key-Ring Lockback

Clam Pack Item# CG002PLCP

Box Item# CG002PL



Key-Ring Lockback

Clam Pack Item# CG002BHCP

Box Item# CG002BH



Key-Ring Included!

- Blade material: 400-series stainless steel
- Handle material: Textured aluminum with stainless steel Lockback
- Ambidextrous nail-nick opening in blade
- Stainless steel fasteners
- Key-ring included
- Blade length: 2.00 in.
- Length closed: 2.12 in.
- Overall length open: 4.60 in.
- Weight: .70 oz.

Z-Frame™ Large

Clam Pack Item# C22CP

Box Item# C22



Black Z-Frame™ Large

Clam Pack Item# C22BCP

Box Item# C22B



- Blade material: 7Cr17 high-carbon stainless steel
- Handle material: Black stainless steel frame with stainless steel Liner-Lock® & deep-carry pocket clip
- Ambidextrous thumb stud
- Stainless steel fasteners
- Blade length: 2.50 in.
- Length closed: 3.65 in.
- Overall length open: 6.12 in.
- Weight: 3.80 oz.

Z-Frame™ Small

Clam Pack Item# C21CP

Box Item# C21



- Blade material: 400-series stainless steel
- Handle material: Stainless steel frame and Liner-Lock®
- Thumb stud
- Stainless steel fasteners
- Handle is strong and lightweight
- Blade length: 1.75 in.
- Length closed: 2.62 in.
- Overall length open: 4.37 in.
- Weight: 1.40 oz.

Compact Tactical

Clam Pack Item# C20146PLCP

Box Item# C20146



LINER-LOCK®

- Blade material: 400-series stainless steel
- Handle material: Black stainless steel frame with stainless steel Liner-Lock®
- Ambidextrous thumb stud
- Stainless steel fasteners
- Stainless steel deep-carry pocket clip
- Blade length: 2.37 in.
- Length closed: 3.25 in.
- Overall length open: 5.75 in.
- Weight: 1.90 oz.

Mini-Tac

Clam Pack Item# 19341

Box Item# 19342



Mini-Tac

Clam Pack Item# 19337

Box Item# 19338



LINER-LOCK®

- Blade material: 7Cr17 high-carbon stainless steel
- Handle material: G-10 with stainless steel frame & Liner-Lock®
- Drop-point blade with thumb perch
- Stainless steel fasteners
- Deep-carry pocket clip
- Blade length: 2.50 in.
- Length closed: 3.50 in.
- Overall length open: 5.87 in.
- Weight: 2.10 oz.

Talon Folder

Clam Pack Item# C36CP

Box Item# C36



LINER-LOCK®

- Blade material: 400-series stainless steel
- Handle material: Black nylon with stainless steel Liner-Lock®
- Ambidextrous thumb stud
- Stainless steel fasteners
- Stainless steel deep-carry pocket clip
- Blade length: 3.25 in.
- Length closed: 4.12 in.
- Overall length open: 7.30 in.
- Weight: 1.90 oz.

X-Frame™ Folder

Clam Pack Item# C20136PLCP
Box Item# C20136PL



X-Frame™ Folder Black

Clam Pack Item# C20136MBCP
Box Item# C20136MB



LINER-LOCK®

- Blade material: 400-series stainless steel
- Handle material: Stainless steel frame & Liner-Lock®
- One-inch serrated blade segment
- Ambidextrous thumb stud
- Stainless steel fasteners & deep-carry pocket clip
- Blade length: 2.50 in.
- Length closed: 3.62 in.
- Overall length open: 5.75 in.
- Weight: 3.00 oz.

Skeleton Folder

Clam Pack Item# C07CP
Box Item# C07



Skeleton Folder Black

Clam Pack Item# C07BCP
Box Item# C07B



LINER-LOCK®

- Blade material: 7Cr17 high-carbon stainless steel
- Handle material: Stainless frame & Liner-Lock®
- One-inch serrated blade segment
- Ambidextrous thumb stud
- Stainless steel fasteners & deep-carry pocket clip
- Blade length: 2.75 in.
- Length closed: 4.12 in.
- Overall length open: 6.87 in.
- Weight: 4.20 oz.

X-Frame™ Liner-Lock®

Clam Pack Item# C008CP
Box Item# C008



LINER-LOCK®

- Blade material: 400-series stainless steel
- Handle material: Aluminum, with stainless steel Liner-Lock®
- One-inch serrated blade segment
- Ambidextrous thumb stud
- Pocket clip for easy carry
- Blade length: 2.875 in.
- Length closed: 3.875 in.
- Overall length open: 6.75 in.
- Weight: 1.80 oz.

Button-Lock Folder

Clam Pack Item# C05CP

Box Item# C05



- Blade material: 400-series stainless steel
- Handle material: Stainless steel frame & Liner-Lock® with button release
- One-inch serrated blade segment
- Ambidextrous thumb stud
- Stainless steel fasteners
- Blade length: 2.75 in.
- Length closed: 3.75 in.
- Overall length open: 6.50 in.
- Weight: 2.60 oz.

Button-Lock Black

Clam Pack Item# C03BCP

Box Item# C03B



BUTTON-LOCK

Tuff-Task

Clam Pack Item# CG004PLCP

Box Item# CG004PL



- Blade material: 400-series stainless steel
- Handle material: Checkered aluminum with stainless steel Liner-Lock®
- One-inch serrated blade segment
- Ambidextrous blade opening
- Stainless steel fasteners & deep-carry pocket clip
- Blade length: 3.00 in.
- Length closed: 4.00 in.
- Overall length open: 7.00 in.
- Weight: 2.50 oz.

Tuff-Task Black

Clam Pack Item# CG004BHCP

Box Item# CG004BH



LINER-LOCK®

S.P.T. Slim Pocket Tactical

Clam Pack Item# C08CP

Box Item# C08



LINER-LOCK®

- Blade material: 7Cr17 high-carbon stainless steel
- Handle material: Black checkered aluminum
- Stainless steel Liner-Lock®
- Stainless steel fasteners
- Stainless steel deep-carry pocket clip
- Blade length: 3.00 in.
- Length closed: 4.25 in.
- Overall length open: 7.25 in.
- Weight: 2.70 oz.

H.A.R.D. Field Knife

Clam Pack Item# C1104CP

Box Item# C1104



FRAME-LOCK

- Blade material: 7Cr17 high-carbon stainless steel
- Stainless steel frame
- Handle material: Contoured & stabilized wood
- Frame-Lock safety
- Ambidextrous thumb stud
- Max-Grip handle design
- Blade length: 4.00 in.
- Length closed: 4.87 in.
- Overall length open: 8.75 in.
- Weight: 5.10 oz.

Pro Predator Lockback

Clam Pack Item# 19325

Box Item# 19326



LOCKBACK

- Blade material: 7Cr17 high-carbon stainless steel
- Handle material: Checkered G10 handle/frame with stainless steel Lockback
- Thumb perch for secure grip
- One-inch serrated segment on blade
- Stainless steel fasteners
- Stainless steel pocket clip
- Blade length: 3.25 in.
- Length closed: 4.12 in.
- Overall length open: 7.87 in.
- Weight: 3.10 oz.

3-in-1 Tool

Clam Pack Item# C53BCP



3-in-1 Tool

Clam Pack Item# C53RCP



- Blade material: 400-series stainless steel
- Handle material: Nylon
- LED light
- Bottle opener
- Stainless steel frame
- Liner-Lock®
- Large nail nick for one-handed opening
- Hole for key-ring attachment
- Blade length: 1.12 in.
- Length closed: 3.00 in.
- Overall length open: 4.00 in.
- Weight: 1.20 oz.



LINER-LOCK®

LED Compact Knife

Clam Pack Item# 7401CP



LED Compact Knife Black

Clam Pack Item# 19248



- Blade material: 400-series stainless steel
- Handle material: Checkered, rubberized grip-panels
- Stainless steel Liner-Lock®
- Aluminum frame
- LED work light
- Ambidextrous thumb stud
- Stainless steel fasteners & attachment clip
- Blade length: 2.50 in.
- Length closed: 4.00 in.
- Overall length open: 6.50 in.
- Weight: 2.70 oz.



LINER-LOCK®

LED Pocket Tool

Clam Pack Item# 19344



LED Pocket Tool Black

Clam Pack Item# 19346



- Blade material: 400-series stainless steel
- Handle material: Stainless steel frame & Liner-Lock®
- Easy-open blade
- Two replaceable double screwdriver bits, Phillips/flat blade
- LED work lights on both ends of tool
- Blade length: 3.00 in.
- Length closed: 4.12 in.
- Overall length open: 7.12 in.
- Weight: 4.60 oz.



LINER-LOCK®



LED Liner-Lock®

Clam Pack Item# C7400CP



LED Light Built In!



- Blade material: 400-series stainless steel
- Handle material: Checkered, rubberized grip panels
- Stainless steel Liner-Lock®
- Aluminum frame
- LED work light
- Ambidextrous thumb disk
- Stainless steel fasteners
- Stainless steel pocket clip
- Blade length: 3.37 in.
- Length closed: 5.00 in.
- Overall length open: 8.25 in.
- Weight: 5.10 oz.



LINER-LOCK®

Natural Stag-Bone Hunter

Clam Pack Item# C8520SBCP



- Blade material: 400-series stainless steel
- Handle material: Natural Stag
- Traditional styling
- Brass handle rivets
- Quality leather sheath
- Lanyard hole
- Blade length: 3.75 in.
- Blade thickness: .112 in.
- Overall length: 7.50 in.
- Weight: 5.10 oz. (with sheath)

Hardwood Hunter

Clam Pack Item# C652CP



- Blade material: 400-series stainless steel
- Handle material: Laminated & stabilized wood
- Traditional styling
- Brass handle rivets
- Quality leather sheath
- Lanyard hole
- Blade length: 3.75 in.
- Blade thickness: .112 in.
- Overall length: 7.00 in.
- Weight: 5.10 oz. (with sheath)

Raptor Tactical/Field Knife

Clam Pack Item# CUS100CP



- Blade material: 9Cr18 Mov high-carbon stainless steel
- Handle material: Textured elastomer
- Blade-back saw
- Full-tang construction with threaded stainless steel butt-cap and striker
- Molded nylon sheath
- Lanyard hole
- Blade length: 6.00 in.
- Blade thickness: .156 in.
- Overall length: 11 in.
- Weight: 10.80 oz. (with sheath)



Metal Commander

Clam Pack Item# C5017CP



- Blade material: Stainless steel blade and tools
- Handle material: Textured aluminum
- Includes knife blade, file, mini screwdriver tip, springless scissors
- Blade length: 1.50 in.
- Length closed: 2.25 in.
- Overall length open: 3.75 in.
- Weight: .50 oz.

Adventurer

Clam Pack Item# C5034CP



- Blade material: Stainless steel blades and tools
- Handle material: Textured aluminum
- Includes large knife blade, small knife blade, bottle opener, can opener, wire stripper, hole punch, slotted screwdriver tip, small slotted screwdriver tip, Phillips screwdriver tip, key ring
- Blade length: 2.50 in. main
- Length closed: 3.5 in.
- Overall length open: 6.25 in.
- Weight: 2.00 oz.

Repairman

Clam Pack Item# C5037CP



- Blade material: Stainless steel blades and tools
- Handle material: Textured aluminum
- Includes large knife blade, small knife blade, scissors, bottle opener, can opener, wire stripper, hole punch, slotted screwdriver tip, small slotted screwdriver tip, saw blade, Phillips screwdriver tip, key ring
- Blade length: 2.50 in. main
- Length closed: 3.5 in.
- Overall length open: 6.25 in.
- Weight: 3.50 oz.

7-inch Fillet Knife

Clam Pack Item# C846CP



- Blade material: Flexible stainless steel
- Handle material: Elastomer sure-grip for comfort
- Serrated segment for rugged cutting
- Lanyard hole
- Molded hard protective sheath
- Blade length: 7.00 in.
- Overall length: 12.50 in.
- Weight: 5.20 oz.

9-inch Fillet Knife

Clam Pack Item# C849CP



- Blade material: Flexible stainless steel
- Handle material: Elastomer sure-grip for comfort
- Two-inch serrated section for rugged cutting
- Molded hard protective sheath
- Blade length: 9.00 in.
- Overall length: 14.50 in.
- Weight: 5.80 oz.

Folding Fillet Knife
Clam Pack Item# C899CP



- Blade material: Flexible stainless steel
- Handle material: Tough & easy-to-clean nylon
- Lock-back locking system
- Stainless steel rivets
- 8-inch lanyard included
- Blade length: 7.00 in.
- Length closed: 7.12 in.
- Overall length open: 13.00 in.
- Weight: 2.80 oz.

**Folding Fish Tool
& 12-Piece Bit Set**
Clam Pack Item# FT8500CP



- 100% stainless steel construction
- Includes: marlin spike, scissors, wire cutter, long-reach needle nose pliers with crimpers for leaders, stops and sleeves. Main blade with serration, Phillips head screwdriver, bottle opener, flat blade screwdriver, and bit driver.
- Locking blades and components
- Nylon sheath
- 32-piece bit set: 3 slotted, 3 Phillips, 6 hex head



Titanium Split-Ring Pliers

Clam Pack Item# FT2401CP



- Stainless steel construction with titanium coating for extra durability
- Sure-grip open-frame design
- Line cutter
- Safety lock
- Molded sheath
- Overall length: 5.00 in.
- Weight: 3.20 oz.

Micro Fishing Tool

Clam Pack Item# MP2875CP



- 100% stainless steel construction
- Includes: needle-nose pliers, leader cutter, saw, main blade, lever-action scissors, wire stripper, scraper, small Phillips screwdriver, small slotted screwdriver, file blade, fish hook eye cleaner, key ring
- Retractable lanyard attaches tool to fishing vest or pants
- Overall length: 4.50 in.
- Weight: 2.60 oz.

9-inch Pro Fishing Pliers

Clam Pack Item# FTP8000CP



- 100% stainless steel construction
- Titanium coated for corrosion protection
- Non-slip elastomer handle grips
- Includes spring-loaded pliers, 3 crimpers for weights and brass sleeves, wire cutters, split-ring remover, lanyard
- Overall length: 9.00 in.
- Weight: 7.60 oz.

7-inch Pro Fishing Pliers

Clam Pack Item# FT6500CP



- 100% stainless steel construction
- Titanium coated for corrosion protection
- Non-slip elastomer handle grips
- Includes spring-loaded pliers, 3 crimpers for weights and brass sleeves, wire cutters, split-ring remover, lanyard
- Overall length: 7.00 in.
- Weight: 6.20 oz.



2-LED Pro Pocket Pliers™

Clam Pack Item# C5899CP

Box Item# C5899



2-LED Pro Pocket Pliers™ Black

Clam Pack Item# C5899BCP

Box Item# C5899B



2 built-in LEDs, 9 functions

- One LED in front, one in rear, click to choose
- Blade material: 400-series stainless steel
- Spring-loaded pliers head
- Sure grip handle inlays
- 3-inch, easy-open knife blade, partial serration
- Scissors, screwdrivers, cap lifter, more
- LED runtime 10–15 hours
- 4 in. closed
- Includes semi-rigid sheath
- Weight: 9.80 oz.



Micro Toolbox™

Clam Pack Item# C3700CP



- Bead-blasted stainless steel
- Includes 3 wrenches, bottle opener, knife blade with partial serration, file blade, nail pick, springless Lever Action scissors, Phillips screwdriver, saw blade, large and small screwdrivers, ruler
- 2.50 in. closed
- Key ring
- Weight: 1.40 oz.

LED Pocket Pliers™ Black

Clam Pack Item# C5799BCP
Box Item# C5799B




Tactical Pocket Pliers™ have built-in LED light

- Built-in LED light: click for constant on
- 400-series stainless steel
- Sure grip handle inlays
- Spring loaded pliers head for easy one-handed operation
- Includes LED light in handle, pliers, wire cutter, main knife blade, file blade with wire stripper, flathead screwdriver, awl, small flathead screwdriver tip, Phillips screwdriver, bottle opener with flathead screwdriver and wire stripper, saw blade, scissors
- Light takes two (2) CR1220 batteries
- 4 in. closed

LED Pocket Pliers™

Clam Pack Item# C5799CP
Box Item# C5799



Pocket Toolbox™

Clam Pack Item# C3900CP



- Bead-blasted stainless steel
- Includes 4 wrenches, bottle opener, knife blade with partial serration, file, slip-joint pliers, Phillips screwdriver, large and small screwdrivers, ruler
- 3.75 in. closed
- Lanyard
- Weight: 2.80 oz.

LED Micro Pliers™ Black

Clam Pack Item# C2899BCP

Box Item# C2899B



LED Micro Pliers™

Clam Pack Item# C2899CP

Box Item# C2899



Pocket-sized Micro Pliers™ have built-in LED light

- Built-in LED light: click for constant on
- 400-series stainless steel
- Sure grip handle inlays
- Spring loaded pliers head for easy one-handed operation
- Includes LED light in handle, pliers, wire cutter, main knife blade, saw blade, keyring, Phillips screwdriver, bottle opener with flathead screwdriver tip and wire stripper, awl, file with nail pick, can opener with small flathead screwdriver tip
- Light takes two (2) CR927 batteries
- 3 in. closed



Diamond Sharpener Large

Item# CM-1



- Diamond-particle coated shaft
- Sharpens knives, tools, scissors, fish hooks—almost anything metal!
- Pocket clip
- Weight: 1.40 oz.
- Overall length: 5.50 in.
- Diamond sharpening surface: 2.50 in.

Diamond Sharpener Medium

Item# CM-2



- Diamond-particle coated shaft
- Sharpens knives, tools, scissors, fish hooks—almost anything metal!
- Pocket clip
- Weight: .60 oz.
- Overall length: 3.75 in.
- Diamond sharpening surface: 2.25 in.

Pocket Sharpening Stone

Item# 19413



- Sharpens quickly and easily
- Designed for sharpening everything from pocket knives to tools and shears
- Leather sheath
- Length: 2.00 in.

Please contact your sales administrator for display assortment information and pricing.

LED Multi-Tool
Quarter Pallet Display
35.5" H x 18.5" W x 21.875" D



G25
Quarter Pallet Display
35.5" H x 18.5" W x 21.875" D



LED Headlamp
Quarter Pallet Display
35.5" H x 18.5" W x 21.875" D




Emergency Area Light
Quarter Pallet Display
47.5" H x 22.625" W x 22.5" D



**G40/G35
Quarter Pallet Display**
49" H x 2" W x 20" D



Power Panel
48" H x 15" W x 16.5" D (Base)
48" H x 15" W x 4.5" D (Display)



2-Sided Display
71" H x 25.75" W x 24.5" D



Free-Standing Sidekick Display

45" H x 21" W x 16.625" D



Rolling Display Cabinet with Spinner

45" H x 20.125" W x 8.75" D (Rolling Display)

24" H x 15" W x 4.5" D (Spinner)



Dumpbin Box

40" H x 16.375" W x 18.375" D



LED Flashlight Header Sign

12.25" H x 46" W x 25" D



*Available for
Sporting Goods
& Hardware
channels*



Acrylic Flashlight Stand

2.875" H x 6" W x 2.375" D



Knife Counter Display

9" H x 11" W x 5.75" D



Folding Acrylic Knife/Flashlight Stand

Large: 1.5" H x 5" W x 2" D

Small: 1.25" H x 3.75" W x 2" D




MODEL IMAGE	PRODUCT NAME	ITEM# CLAM PACK / BOX	BATTERY TYPE	MAX. LUMENS	RUN TIME	BEAM DIST.	OVERALL SIZE (IN.)	WEIGHT (INCL. BATTERIES)	PAGE #
	A25	19247	4 x AAA	226	5 h	205 m	5.50	10.4 oz	21
	A20	19267	3 x AAA	171	6 h 15 min	64 m	3.67	4.4 oz	21
	A15	19266	3 x AAA	194	3 h 45 min	127 m	3.90	5 oz	21
	A9	19364 / 19335	3 x AAAA	20			7.03		22
	A10	19246	2 x AAA	66	1 h 30 min	70 m	5.48	3.2 oz	22
	A5	19245	1 x AAA	26	7 h 15 min	20 m	3.74	2 oz	22
	EAL20	CE7124HGB	4 x D	375	100 h	N/A	8.25	32.02 oz	30
	EAL15	C7050CP	4 x C	60	50 h	N/A	7.50	16.06 oz	30
	EAL10	C7040CP	4 x AA	17	30 h	N/A	5.75	9 oz	31
	EAL5	C7044CP	4 x AAA	15	40 h	N/A	5.375	4.6 oz	31
	G50	TT8607CP / 19299	3 x AAA	166	7 h	143 m	4.80	5.8 oz	17
	G45 Black	19300 / 19356	3 x AAA	135	8 h 30 min	53 m	4.60	3.6 oz	17
	G45 Titanium	TT7345SCP	3 x AAA	135	8 h 30 min	53 m	4.60	3.6 oz	17
	G40	TT1006CP	3 x AAA	130	11 h	52 m	6.03	5 oz	18
	G35	TT1106CP	3 x AAA	111	10 h 15 min	47 m	6.03	5.2 oz	18
	G30	TT8606CP / 19298	2 x AA	121	2 h	146 m	6.46	5.6 oz	17

MODEL IMAGE	PRODUCT NAME	ITEM# CLAM PACK / BOX	BATTERY TYPE	MAX. LUMENS	RUN TIME	BEAM DIST.	OVERALL SIZE (IN.)	WEIGHT (INCL. BATTERIES)	PAGE #
	G25 Black	TT7547BLCP / 19355	2 x AA	83	9 h 45 min	41 m	6.05	3.6 oz	18
	G25 Titanium	TT7547CP	2 x AA	83	9 h 45 min	41 m	6.05	3.6 oz	18
	G20	TT7817CP / 19304	2 x AAA	36	12 h 15 min	22 m	5.65	2.4 oz	19
	G19	19384	1 x AAA				4.02		19
	G15	TT75331CP	1 x AAA	32	2 h 45 min	24 m	3.70	1.5 oz	19
	G10 Black	TT7830CP	1 x AAA	32	2 h 45 min	24 m	3.70	1.2 oz	20
	G10 Titanium	TT7831CP	1 x AAA	32	2 h 45 min	24 m	3.70	1.2 oz	20
	G5	TT7839CP	4 x AG5	33	45 min	24 m	2.45	.4 oz	20
	HL7	19284 / 19273	3 x AAA	196	5 h 45 min	109 m	N/A	4.4 oz	26
	HL7R	TT7498CP / 19274	3 Ni-MH Recharge- able	150	3 h	114	N/A	4.4 oz	26
	HL6	TT7468CP / 19268	3 x AAA	181	6 h 15 min	111 m	N/A	4.2 oz	26
	HL5	TT7041CP / 19351	3 x AAA	175	3 h 45 min	56 m	N/A	4.4 oz	27
	HL4	19291	3 x AAA	144	6 h 15 min	57 m	N/A	4.4 oz	27
	HL3	TT7454CP / 19350	3 x AAA	60	12 h 30 min	43 m	N/A	4.4 oz	27
	HP21	19282	4 x D	1317	2 h 15 min	260 m	15.50	2.8 lbs	11
	HP21R	19390	Ni-MH Recharge- able				15.50	2.8 lbs.	11

MODEL IMAGE	PRODUCT NAME	ITEM# CLAM PACK / BOX	BATTERY TYPE	MAX. LUMENS	RUN TIME	BEAM DIST.	OVERALL SIZE (IN.)	WEIGHT (INCL. BATTERIES)	PAGE #
	HP17	HP8417CP	3 x D	615	15 h 15 min	269 m	13.12	1.9 lb	11
	HP17TAC	19281	3 x D	615	15 h 15 min	269 m	13.12	1.9 lb	13
	HP14	HP8414CP / 19280	4 x AA	339	4 h 45 min	175 m	8.38	14.2 oz	11
	HP7	HP8407CP / 19279	4 x AAA	251	5 h 45 min	196 m	5.58	7.2 oz	12
	HP7 Titanium	HP8420-TCP-P3 / 19235	4 x AAA	251	5 h 45 min	196 m	5.58	7.2 oz	12
	HP7TAC	HP8407AFCP	4 x AAA	251	5 h 45 min	196 m	5.58	7.2 oz	13
	HP6	HP8406CP / 19278	2 x AA	170	5 h	104 m	6.62	4.6 oz	12
	HP6TAC	HP8406AFCP	2 x AA	170	5 h	104 m	6.62	4.6 oz	13
	HP5	HP8405CP / 19277	1 x AA	121	4 h 30 min	78 m	4.65	3 oz	12
	HP5TAC	HP8405AFCP	1 x AA	121	4 h 30 min	78 m	4.65	3 oz	13
	HP4	HP8404CP / 19276	2 x AAA	95	4 h 15 min	57 m	5.54	2.2 oz	12
	PX50	TT7456CP	4 x AA	131	9 h 15 min	195 m	6.50	8.4 oz	14
	PX45	19285 / 19265	3 x AAA	212	7 h 15 min	186 m	5.20	5.8 oz	14
	PX25	TT7736CP / 19270	3 x AAA	208	6 h 15 min	128 m	4.70	4.2 oz	14
	PX20	19286 / 19271	3 x AAA	125	5 h 30 min	53 m	3.95	3.2 oz	15
	PX10	19269	3 x AAA	59	14 h	39 m	3.95	3 oz	15
	PX5	HP8313CP / 19275	4 x AG13	44	1 h 45 min	21 m	2.75	1.2 oz	15
	TX40	TT7736TSCP / 19272	3 x AAA	164	7 h 45 min	158 m	5.94	5.4 oz	16
	TX10	TT77364CP	3 x AAA	73	8 h 15 min	36 m	3.95	3 oz	16

MODEL IMAGE	PRODUCT NAME	ITEM# CLAM PACK / BOX	BLADE SIZE (IN.)	OVERALL SIZE (IN.)	WEIGHT (OZ.)	LOCK SYSTEM	BLADE MATERIAL	HANDLE MATERIAL	PAGE #
	3-in-1 Tool	C53BCP	1.12	4.00	1.20	Liner-Lock®	400-series stainless steel	Nylon	45
	3-in-1 Tool	C53RCP	1.12	4.00	1.20	Liner-Lock®	400-series stainless steel	Nylon	45
	7-Inch Fillet Knife	C846CP	7.00	12.50	5.20	N/A	Stainless steel	Kraton®	49
	9-Inch Fillet Knife	C849CP	9.00	14.50	5.80	N/A	Stainless steel	Kraton®	49
	Adventurer	C5034CP	2.5 main/ 1.5 small	6.25	2.00	N/A	Stainless steel	Textured aluminum	48
	Black Magic Liner-Lock®	CG006CP / CG006	3.35	7.75	3.20	Liner-Lock® + Double-Lock™	7Cr17	Checkered aluminum	37
	Button-Lock Folder	C05CP / C05	2.75	6.50	2.60	Liner-Lock®	400-series stainless steel	Stainless steel	43
	Button-Lock Black	C03BCP / C03B	2.75	6.50	2.60	Liner-Lock®	400-series stainless steel	Stainless steel	43
	Compact Tactical	C20146PLCP / C20146	2.37	5.75	1.90	Liner-Lock®	400-series stainless steel	Black stainless steel	41
	Dark Force I	19339 / 19340	3.50	8.25	5.00	Liner-Lock® + Double-Lock™	7Cr17	Grip-enhanced G-10	39
	Dark Force II	19357 / 19358	3.50	8.25	5.00	Liner-Lock® + Double-Lock™	7Cr17	Grip-enhanced G-10	39
	Folding Fillet Knife	C899CP	7.00	13.00	2.80	Lockback	Stainless steel	Nylon	50
	Ghost I	19311 / 19312	3.25	7.87	3.80	Liner-Lock® + Double-Lock™	7Cr17	Grip-enhanced aluminum	39
	Ghost II	19313 / 19314	3.50	8.00	3.70	Liner-Lock® + Double-Lock™	7Cr17	Grip-enhanced aluminum	39
	H.A.R.D. Field Knife	C1104CP / C1104	4.00	8.75	5.10	Frame-Lock	7Cr17	Wood	44
	Hardwood Hunter	C652CP	3.75	7.00	5.10 in sheath	N/A	400-series stainless steel	Hardwood	47
	Key-Ring Lockback	CG002PLCP / CG002PL	2.00	4.60	0.70	Lockback	400-series stainless steel	Textured aluminum	40
	Key-Ring Lockback	CG002BHCP / CG002BH	2.00	4.60	0.70	Lockback	400-series stainless steel	Textured aluminum	40
	LED Compact Knife	C7401CP	2.50	6.50	2.70	Liner-Lock®	400-series stainless steel	Rubberized handle	45
	LED Compact Knife Black	19248	2.50	6.50	2.70	Liner-Lock®	400-series stainless steel	Rubberized handle	45
	LED Liner-Lock®	C7400CP	3.375	8.25	5.10	Liner-Lock®	400-series stainless steel	Rubberized handle	46
	LED Pocket Tool	19344	3.00	7.12	4.60	Liner-Lock®	400-series stainless steel	Stainless steel frame	46
	LED Pocket Tool Black	19346	3.00	7.12	4.60	Liner-Lock®	400-series stainless steel	Stainless steel frame	46
	Metal Commander	C5017CP	1.50	3.75	0.50	N/A	Stainless steel	Textured aluminum	48

MODEL IMAGE	PRODUCT NAME	ITEM# CLAM PACK / BOX	BLADE SIZE (IN.)	OVERALL SIZE (IN.)	WEIGHT (OZ.)	LOCK SYSTEM	BLADE MATERIAL	HANDLE MATERIAL	PAGE #
	Mini-Tac	19341 / 19342	2.50	5.87	2.10	Liner-Lock®	7Cr17	G-10 with stainless steel frame	41
	Mini-Tac	19337 / 19338	2.50	5.87	2.10	Liner-Lock®	7Cr17	G-10 with stainless steel frame	41
	Natural Stag- Bone Hunter	C8520SBCP	3.75	7.50	5.10 in sheath	N/A	400-series stainless steel	Stag	47
	P.D.T. Police Duty Tactical	19305 / 19306	3.25	8.12	4.20	Liner-Lock® + Double-Lock™	7Cr17	Grip-enhanced aluminum	38
	Pro Predator Lockback	19325 / 19326	3.25	7.87	3.10	Lockback	7Cr17	Checkered G-10	44
	Rapid Response® 3.90	19213 / 19393	3.90	8.75	4.80	Liner-Lock® + Max-Lock™	High-carbon stainless steel	Fiberglass-filled textured nylon	36
	Rapid Response® 3.90 Black	19214 / 19394	3.90	8.75	4.80	Liner-Lock® + Max-Lock™	High-carbon stainless steel	Fiberglass-filled textured nylon	36
	Rapid Response® 3.00	19211 / 19391	3.00	7.00	3.70	Liner-Lock® + Max-Lock™	High-carbon stainless steel	Fiberglass-filled textured nylon	36
	Rapid Response® 3.00 Black	19212 / 19392	3.00	7.00	3.70	Liner-Lock® + Max-Lock™	High-carbon stainless steel	Fiberglass-filled textured nylon	36
	Raptor Tactical/ Field Knife	CUS100CP	6.00	11.00	10.80 in sheath	N/A	High-carbon stainless steel	Textured Elastomer	47
	Repairman	C5037CP	2.5 main/ 1.5 small	6.25	3.50	N/A	Stainless steel	Textured aluminum	48
	R.T.O.-I Rescue Team Operator	19307 / 19308	3.25	8.12	4.20	Liner-Lock® + Double-Lock™	7Cr17	Grip-textured aluminum	38
	R.T.O.-II Rescue Team Operator	19309 / 19310	3.25	8.12	4.20	Liner-Lock® + Double-Lock™	7Cr17	Grip-textured aluminum	38
	Skeleton Folder	C07CP / C07	2.75	6.87	4.20	Liner-Lock®	7Cr17	Brushed stainless steel	42
	Skeleton Folder Black	C07BCP / C07B	2.75	6.87	4.20	Liner-Lock®	7Cr17	Black stainless steel	42
	S.P.T.	C08CP / C08	3.00	7.25	2.70	Liner-Lock®	7Cr17	Black checkered aluminum	44
	Tactical Liner-Lock®	C19CP / C19	3.35	8.00	3.50	Liner-Lock® + Double-Lock™	7Cr17	Black aluminum	38
	Talon Folder	C36CP / C36	3.25	7.30	1.90	Liner-Lock®	400-series stainless steel	Contoured checkered nylon	41
	Tuff-Task	CG004PLCP / CG004PL	3.00	7.00	2.50	Liner-Lock®	400-series stainless steel	Black checkered aluminum	43
	Tuff-Task Black	CG004BHCP / CG004BH	3.00	7.00	2.50	Liner-Lock®	400-series stainless steel	Black checkered aluminum	43
	X-Frame Folder	C20136PLCP / C20136PL	2.50	5.75	3.00	Liner-Lock®	400-series stainless steel	Stainless steel	42
	X-Frame Folder Black	C20136MBCP / C20136MB	2.50	5.75	3.00	Liner-Lock®	400-series stainless steel	Stainless steel	42
	X-Frame Liner-Lock®	C008CP / C008	2.87	6.75	1.80	Liner-Lock®	400-series stainless steel	Aluminum	42
	Z-Frame Large	C22CP / C22	2.50	6.12	3.80	Liner-Lock®	7Cr17	Brushed stainless steel	40
	Z-Frame Large Black	C22BCP / C22B	2.50	6.12	3.80	Liner-Lock®	7Cr17	Black stainless steel	40
	Z-Frame Small	C21CP / C21	1.75	4.37	1.40	Liner-Lock®	400-series stainless steel	Stainless steel	40

MODEL IMAGE	PRODUCT NAME	ITEM# CLAM PACK / BOX	BLADE SIZE (IN.)	OVERALL SIZE (IN.)	WEIGHT (OZ.)	LOCK SYSTEM	BLADE MATERIAL	HANDLE MATERIAL	PAGE #
	2-LED Pro Pocket Pliers	C5899CP / C5899	3.25	7.25	9.80	Liner-Lock®	400-series stainless steel	Stainless steel / rubber	53
	2-LED Pro Pocket Pliers Black	C5899BCP / C5899B	3.25	7.25	9.80	Liner-Lock®	400-series stainless steel	Stainless steel / rubber	53
	7-Inch Pro Fishing Pliers	FT6500CP	N/A	7.00	6.20	N/A	Titanium-coated stainless steel	Rubberized handle	51
	9-Inch Pro Fishing Pliers	FTP8000CP	N/A	9.00	7.60	N/A	Titanium-coated stainless steel	Rubberized handle	51
	Folding Fish Tool & 12-Piece Bit Set	FT8500CP	3.25	8.00	13.60	N/A	Stainless steel	Bead blasted / rubber	50
	LED Micro Pliers	C2899CP / C2899	2.25	4.50	4.40	N/A	400-series stainless steel	Stainless / rubber	55
	LED Micro Pliers Black	C2899BCP / C2899B	2.25	4.50	4.40	N/A	400-series stainless steel	Stainless / rubber	55
	LED Pocket Pliers	C5799CP / C5799	2.00	6.00	11.80	N/A	400-series stainless steel	Stainless / rubber	54
	LED Pocket Pliers Black	C5799BCP / C5799B	2.00	6.00	11.80	N/A	400-series stainless steel	Stainless / rubber	54
	Micro Fishing Tool	MP2875CP	1.50	4.50	2.60	N/A	400-series stainless steel	Bead-blasted	51
	Micro Toolbox	C3700CP	1.75	4.00	1.40	N/A	stainless steel	Bead-blasted	54
	Pocket Toolbox	C3900CP	2.50	6.00	2.80	N/A	stainless steel	Bead-blasted	55
	Titanium Split-Ring Pliers	FT2401CP	N/A	5.00	3.20	N/A	Titanium-coated steel	ABS	51
	Diamond Sharpener Large	CM-1	2.50 diamond surface	5.50	1.40	N/A	N/A	Aluminum	56
	Diamond Sharpener Medium	CM-2	2.25 diamond surface	3.75	.60	N/A	N/A	Aluminum	56
	Pocket Sharpening Stone	19413	N/A	2.00	N/A	N/A	N/A	N/A	56



P.O. Box 5821 • Portland, OR 97228
503-234-4545 • Fax 503-234-4422
Toll Free 1-800-426-5858
www.COASTportland.com



Follow
COAST

