



FEATURES:

- Cross stacking and vertical stacking on both ends.
- Mates to model #1581, 2854 or any standard banana jack.

MATERIALS:

Conn: Standard Stacking Banana Plug

Material: Spring - Beryllium Copper per QQ-C-533, Alloy 172, cond. HT.

Plug Body – Brass per QQ-B-626, Alloy 360, $\frac{1}{2}$ Hard.

Finish: Nickel plated per QQ-N-290, Class 2, 200/300 microinches.

Insulation: Polypropylene molded to plug body and wire.

Color: Matches color of wire.

Retractile Cord: 20 AWG, stranding 42 x 36 t.c., PVC insulated, 3.71 (.146) O.D.

Color: See Ordering Information.

RATINGS:

Operating Temperature: +55°C. (+131°F.) Max.

Operating Voltage: Hand-held testing: 30 VAC/60VDC Max.

Hands free testing in controlled voltage environments: 270 VDC Max.

Current: 5 Amperes

ORDERING INFORMATION: Model 2484-*

*= Color, -0 Black, -2 Red

Ordering Example: 2484-2 Adapter Color is Red

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

2484-2 2484-0