

Search Product:

Submit

[ [Advanced](#) ]

- ? [Adapters & power supplies](#)
- ? [Batteries & chargers](#)
- ? [Cables & accessories](#)
- ? [Connectors](#)
- ? [Consumer products & pc acc.](#)
- ? [Electronic components](#)
- ? [High-q tools & dmm's](#)
- ? [Led products & lamps](#)
- ? [Light products](#)
- ? [Loudspeakers & pa systems](#)
- ? [Perel tools](#)
- ? [Security products](#)
- ? [Velleman kits & oscilloscopes](#)

[ROHS Info](#)

[HIGH -Q TOOLS & DMM'S](#) > [MULTIMETERS](#) > [CLAMP METERS](#) >



## ECONOMIC DIGITAL CLAMP METER

Order Code: DCM266L



### Features

- ? digital clamp meter
- ? 3 1/2 LCD display with automatic polarity indication
- ? data-hold function
- ? AC current measurements: max. 1000A
- ? insulation test: max. 2000Mohm (if used with optionalDCMIT)
- ? voltage measurements: AC (max. 750V) and DC (max. 1000V)
- ? resistance measurements: max. 20Kohm
- ? with carrying bag

### Specifications

- ? DC voltage: 1000V
  - ? basic accuracy:  $\pm 0.8\%$
  - ? input impedance: > 9Mohm
  - ? maximum input: 1000V
- ? AC voltage: 750V
  - ? basic accuracy:  $\pm 1.0\%$
  - ? input impedance: > 9Mohm
  - ? frequency range: -
  - ? maximum input: 750V
- ? DC current: -
  - ? basic accuracy: -
  - ? overload protection: -
- ? AC current: 200/1000A
  - ? basic accuracy:  $\pm 2.0\%$
  - ? overload protection: 1200A for 60 seconds
- ? resistance: 200/20k (insulation test : 20M/2000M)
  - ? basic accuracy:  $\pm 1.0\%$  (  $\pm 2.0\%$  for insulation test)
  - ? overload protection: 500V
- ? capacitance: -
  - ? accuracy: -
- ? inductance: -
  - ? accuracy: -
- ? frequency: -
  - ? basic accuracy: -
  - ? overload protection: -
- ? temperature: -
  - ? basic accuracy: -
- ? overrange: yes "1"
- ? continuity buzzer: yes
- ? transistor test: -
- ? diode test: -
- ? low-battery indication: yes "BAT"
- ? maximum display: 3 1/2
- ? LCD display size:-
- ? ranging mode: manual
- ? data hold: yes
- ? backlight: no
- ? dimensions: 9.1" x 1.5" x 3.5"
- ? weight (with battery):  $\pm 11.3\text{oz}$
- ? power supply: 9V battery (incl.)
- ? packaging: -
- ? accessories: manual / test leads / battery / carrying bag
- ? auto power-off: no

### Files

- ? [dcm266lgb.pdf](#)
- ? [dcm266lfront.pdf](#)

### Stock Info

- ? Inner carton:
- ? Outer Carton: 20
- ? EAN Barcode: 5410329274856
- ? Packaging: Box (Carton)