




SHEET 1 OF 1

SUGGESTED PANEL CUTOUT

MATERIALS

SPECIFICATIONS

BODY:
Phenolic (PF), UL94 V-2

ACTUATOR:
Polyamide 6/6 (PA66), UL94 V-2
Brass

SEALING MEMBRANE:
Polyvinyl Chloride (PVC)

SPRING:
Piano Wire

MOBILE CONTACT:
Silver Plated Copper

CONTACTS:
Silver Clad Copper

RIVETS:
Copper

TERMINALS:
Brass

FUNCTION:
2P2T ON-OFF-ON

RATINGS:
ANSI/UL 508 and CAN/CSA C22.2 No.14 (E195908):
20A 125VAC [cURus]
15A 277VAC [cURus]
2HP 125/250VAC [cURus]

CONTACT RESISTANCE:
Initial: 50mΩ Max. at 50VAC

ELECTRICAL LIFE:
6,000 Cycles [cURus]

TEMPERATURE:
Operating: -20°C to 55°C [cURus]

INGRESS PROTECTION:
IP54

APPROVALS:
cURus RoHS COMPLIANT

COLORS AND MARKINGS

BODY COLOR:
Black

ACTUATOR COLOR:
Black

MARKINGS:
None

MARKING COLOR:
None