





OUTSIDE DIAMETER		THREADS PER INCH	DEPTH OF THREAD	RADIUS OF THREAD
MAJOR CREST OF THREAD	MINOR ROOT OF THREAD			
MIN. .206" (5.23mm)	-----	25.4	.011" MIN. (.28mm)	.0116" (.29mm)
MAX. .210" (5.33mm)	MAX. .188" (4.77mm)			

JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	MSCP ±25%	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
8669	1.4	.060	.010	0.13	3,000	C-2R
1767	2.5	.200	.200	2.51	500	C-2R
7318	5.0	.060	.050	0.63	100,000	C-2R
7319	5.0	.115	.150	1.89	40,000	C-2R
342	6.0	.040	.030	0.38	10,000	C-2V
1768	6.0	.200	.630	7.92	1,000	C-2R
7320	6.3	.040	.030	0.38	20,000	C-2V
1775	6.3	.075	.230	2.89	1,000	C-2R
378	6.3	.200	.400	5.03	50,000	C-2F
7323	6.3	.200	.550	6.91	5,000	C-2R
389	10.0	.040	.080	1.01	30,000	C-2F
7326	12.0	.040	.120	1.51	10,000	C-2R
8362	14.0	.080	.300	3.77	50,000	C-2F
383	14.0	.080	.500	6.29	2,500	C-2F
8162	14.0	.100	.500	6.29	50,000	C-2F
8536	18.0	.040	.150	1.89	10,000	C-2F
8437	22.0	.040	.300	3.77	2,000	C-2F
399	28.0	.040	.300	3.77	25,000	C-2F
369	28.0	.040	.340	4.27	4,000	C-2F

METRIC



THIRD ANGLE
PROJECTION

DIMENSIONS ARE
IN MILLIMETERS

TOLERANCE UNLESS
OTHERWISE SPECIFIED

1 PL +/- 0.2
2 PL +/- 0.20
ANGLE +/- 0

JKL

COMPONENTS CORPORATION

TITLE

T-1 3/4 STANDARD MIDGET SCREW BASE LAMP

DRAWN BY

APPVD BY DATE

SIZE

FSCM NO.

DRAWING

NO.

SCREW BASE T-1 3/4--15.9

L. WENGSTROM

QC 11/17/00

A

55335

REV.
NO.

DESCRIPTION/ECO
NUMBER

APPVD
DATE

- CAD DRAWING -

MANUAL REVISIONS NOT PERMITTED

SCALE

NONE

RELEASED
DATE

11/17/00

REVISION
DATE

REV.
NO.

SHEET

1 OF 1

RELEASE & CANCEL 7312, FS23, 8692

11/17/00