



NOTES: UNLESS OTHERWISE SPECIFIED

1. CONSTRUCTION:
- HOUSING: MOLDED NYLON. AVAILABLE IN TEN COLORS.
- FRAME: BRASS. NICKEL PLATED.
- CONTACT: BeCu OR PHOSPHOR BRONZE. NICKEL PLATED.

2. PERFORMANCE:
- MAXIMUM CURRENT: 15 AMPS
- MAXIMUM VOLTAGE: 3500 VRMS
- MAXIMUM TEMPERATURE: 200°F (93°C)



ACTUAL SIZE

		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES ±	
--	--	---	--