

Search:

Select Location:

[Enclosures](#) | [Contract Manufacturing](#) | [Products](#) | [Company info](#) | [News & Events](#) | [Contacts](#) | [Downloads](#)

Product card: PC 25 / 22-FC3



Sample photo

Including: Base, terminal compartment cover with EPDM gasket and screws for mounting plate/DIN-rail. -3 and -L3 versions:
Transparent cover with PUR gasket, hinges, locking devices; FC version: Closed PC frame front plate with PUR gasket and cover screws.

Support items:

- [Dimensional drawing \(inch\)](#)
- [Dimensional drawing \(mm\)](#)
- [Accessories](#)

Product nbr: 7520241
Description: Enclosure, PC
Remarks: With front plate frame
Package: 1
Unit: PCS
Product group: CARDMASTER
EAN: 6418074059376

Dimensions:

Length (mm): 257
Width (mm): 219
Height (mm): 135
Length (inch): 10.1
Width (inch): 8.6
Height (inch): 5.3

Materials:

Material: Polycarbonate
Base colour: RAL 7035
Gasket material: EPDM and Polyurethane

Temperatures:

Min temperature °C (short term): -40
Max temperature °C (short term): 120
Min temperature °C (continuous): -40
Max temperature °C (continuous): 80
Min temperature °F (short term): -40
Max temperature °F (short term): 250
Min temperature °F (continuous): -40
Max temperature °F (continuous): 175

Rating:

Ingress Protection (EN 60529):	IP 65
Impact Resistance (EN 50102):	IK 08/07
Electrical insulation:	Totally insulated
Halogen free (DIN/VDE 0472, Part 815):	Yes
UV resistance:	UL 508
Flammability Rating (UL 746 C 5):	UL 94 5V
Glow Wire Test (IEC 695-2-1) °C:	960
NEMA Class:	NEMA 1, 3, 3R, 4X, 12, 13

Certificates:

Underwriters Laboratories
Fimko
Europe EN 50298: 1998
UL Canada
Gost R







Product is connected to following catalogs:

[Fibox catalogue](#) : [CARDMASTER](#) : [PC/ABS 25/22](#)


[Enclosure](#)
[search](#)

[Back to catalog](#)


[Legal Notice](#)











25/22-3



25/22-FC3



25/22-C3



25/22-3

25/22-FC3

25/22-C3