



Sample photo

Order symbol: PCM 175/100 G
Product nbr: 6016321
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074038128
El. number:
Finland: 3421646
Electric No. Denmark: 8212027242
Electric No. Italy: 7341065
Electric No. Sweden: 2535339

Including: Base with metric knock-outs and TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:			Accessories:		
mm:	180	180	100	MIN 15	DIN-15 Mounting rail
inch:	7.1	7.1	3.9	MIV 15	DIN-35 Mounting rail
			FP A 175/180	Front plate (Aluminium)	
			HFP 180	Front plate hinge series	
			FP 22046	Wall fastening lug (4 pcs)	
Materials:			Rating:		
Material:	Polycarbonate		Ingress Protection (EN 60529): IP66/67		
Base colour:	RAL 7035 -light grey		Impact Resistance (EN 62262): IK08		
Cover screws material:	Polyamide		Electrical insulation: Totally insulated		
Cover colour:	RAL 7035 -light grey		Halogen free (DIN/VDE 0472, Part 815): 1		
Cover screws colour:	Grey		UV resistance: UL 508		
Gasket material:	TPE		Flammability Rating: UL 746C 5V		
Temperatures:			Glow Wire Test (IEC 695-2-1) °C: 960		
Temperature °C (short term):	-40 ... 120 °C		NEMA Class: NEMA 1, 4, 4X, 6, 12, 13		
Temperature °C (continuous):	-40 ... 80 °C		Certificates:		
Temperature °F (short term):	-40 ... 250 °F		Germanischer Lloyd (GL)		
Temperature °F (continuous):	-40 ... 175 °F		SGS Fimko		
Accessories:			Gost R		
MIV 175	Mounting plate (Galvanized steel)				

