

Replacement die - CRIMPFOX-M SC 6/DIE - 1212085

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Die, for Crimpfox-M, for non-insulated slip-on sleeves 0.5 - 6 mm², packed in a serial storage box

Key commercial data

Packing unit	0
Minimum order quantity	1
Catalog page	Page 280 (CL2-2011)
GTIN	 4 046356 454551
Custom tariff number	82032000
Country of origin	SWEDEN

Technical data

General

Length (b)	114 mm
Height	25.5 mm
Width (a)	75 mm
Color	black
Weight	74 g
Die station	Crimping position 1
Min. cross section	0.5 mm²
Max. cross section	6 mm²
AWG min	22
AWG max	16
Die station	Crimping position 2
Min. cross section	1.5 mm²
Max. cross section	2.5 mm²
AWG min	16
AWG max	14
Die station	Crimping position 3
Min. cross section	4 mm²
Max. cross section	6 mm²
AWG min	12
AWG max	10

Replacement die - CRIMPFOX-M SC 6/DIE - 1212085

Technical data

General

Compression	B crimp
Type of contact	Slip-on sleeve

Classifications

eclass

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	21043811
eCl@ss 7.0	21043811

etim

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186

unspsc

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518

Approvals

Approvals

Approvals

GOST

Ex Approvals

Approvals submitted

Approval details

GOST 
--

