



1. DESIGNATION

Plastic plugs with one-piece hinged casing 10/16A

2. FUNCTION

- ① Used to connect a Class I appliance and its cable to a socket
- ② Allows the customer to carry out his own wiring

3. RANGE

Right outlet : Cat. No. 502 15/34/35

Side outlet: 502 16/38/39

4. COMMON GENERAL CHARACTERISTICS

Each plug is made up of the following elements:
1 one-piece hinged body supporting 2 earth pins and 1 phase tulip contact with integrated cable grip

5. SPECIFIC CHARACTERISTICS

- Plug with left or right side outlet
- Cable grip with integrated tab
- Body supporting 2 phase pins for wiring by screw terminal and 1 earth tulip contact for wiring by screw terminal
- Product closed using 1 screw
- For round wire $\varnothing$ 11 mm max.
- Cable outlet can be cut to size

6. PERFORMANCE

6.1 Product performance

- 10/16 A
- Reliability:
 - Shock tests: 2 Joules
 - use: 5000 insertions and 5 000 removals
 - IP 2.0

6.2 Material performance

Polypropylene fireproof: 750 °C

7. CONFORMITY TO STANDARDS AND APPROVALS

NF C 61-303
Approved NF USE

8. USAGE PRECAUTIONS

Position the cable correctly within the cable grip tabs

9. PACKAGING

Box with cardboard inner