


Capacitor, film, 1 uF, +/-10% Tol, General Purpose, 50VDC@125C



Note: 'l' correspond to the letters used in the product bulletin

Dimensions (mm)		
Symbol	Dimension	Tolerance
L	7.3	+/-0.4
W	6.1	+/-0.4
T	3.1	MAX

General Information

Supplier: KEMET

Specifications

Capacitance:	1 uF
Dielectric:	Metallized PEN (Stacked)
Rated Temperature:	125C
Voltage @ rated temp:	50VDC
Voltage AC:	40VAC
Tolerance:	+/-10%
Body Type:	Surface Mount
Chip Size:	2824
Application:	General Purpose
Temperature Range:	-55/+125C
Dissipation Factor @ 1 kHz:	0.8%
Insulation Resistance:	400 MOhm
Maximum dVdT:	100 v/us

Packaging Specifications

Package Kind:	T&R
Package Size:	330mm
Package Quantity:	2250

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.