

## UM108-PROFIL CM - 2959492

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Drawn section panel mounting base, 108 mm narrow module.

The figure shows the variant UM 45-Profil CM

### Key Commercial Data

Packing unit	1 M
GTIN	 4 017918 086145
GTIN	4017918086145
Weight per Piece (excluding packing)	55.840 g
Custom tariff number	39162010
Country of origin	Germany

### Technical data

#### General

Housing material	PVC
Color (RAL)	green

#### Dimensions

Width	108 mm
-------	--------

#### Standards and Regulations

Flammability rating according to UL 94	V0
--	----

#### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
------------	---

# UM108-PROFIL CM - 2959492


## Technical data

### Environmental Product Compliance

	No hazardous substances above threshold values
--	--

## Drawings

Dimensional drawing



## Classifications

### eCl@ss

eCl@ss 4.0	27180401
eCl@ss 4.1	27180401
eCl@ss 5.0	27180506
eCl@ss 5.1	27180506
eCl@ss 6.0	27180802

### ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC001031

### UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 13.2	31261501

## UM108-PROFIL CM - 2959492

### Accessories

#### Accessories

#### Component housing cover

Covering hood - UM108-A/U CM - 2854898



Press-drawn section housings, Cover, 73 mm wide, width: 73 mm, color: transparent, Note: length of the cover = length of the press-drawn section used

---

Covering hood - UM-A/U N 73 CM - 2706852



Press-drawn section housings, Cover, 73 mm wide, width: 73 mm, color: transparent, Note: length of the cover = length of the press-drawn section used

---

#### Component housing lower part

Side element - UM108-LG 10 - 2959780



Profile housing and board base, 10 mm wide module, consisting of two side elements

---

#### Mounting material

Foot element - UM108-FE - 2959463



Foot element, 107.5 mm wide, for mounting on NS 32 or NS 35/7.5, below profile housing UM 108.

## UM108-PROFIL CM - 2959492

### Accessories

Mounting flange - UMK-BF - 2976077



Mounting flange, for mounting directly on the wall

---

### Panel mounting base side part

Side element - UM108-SEFE/R - 2959683

Side element with foot, 5 mm wide (right), for mounting on NS 32 or NS 35/7.5. PCB width: 107.5 mm



Side element - UM108-SEFE/L - 2959696

Side element with foot, 5 mm wide (left), for mounting on NS 32 or NS 35/7.5. PCB width: 107.5 mm



Side element - UM108-SEPEF/L - 2906490

Press-drawn section housings, Lateral element (left), with snap-on foot and PE contact, color: green



Side element - UM108-SE - 2959476

Side element, 5 mm wide, PCB width: 107.5 mm



## UM108-PROFIL CM - 2959492

### Accessories

Side element - UM108-SEFE/R-A60 - 2959706



Side element, with foot, tall version, right-hand, for 60 mm wide U-shaped cover.

---

Side element - UM108-SEFE/R-A73 - 2959719



Side element, with foot, tall version, right-hand, for 73 mm wide U-shaped cover.

---

Side element - UM108 N-SEFE/R-A73 - 2709354



Side element, with foot, low-profile version, right-hand, for 73 mm wide U-shaped cover.

---

Side element - UM108-SEFE/L-A60 - 2959722



Side element, with foot, tall version, left-hand, for 60 mm wide U-shaped cover.

---

Side element - UM108-SEPEF/L-A60 - 2906500



Side element with foot, tall design, left-hand, for 60 mm wide U-shaped cover, with PE contact to the DIN rail.

---

## UM108-PROFIL CM - 2959492

### Accessories

Side element - UM108-SEFE/L-A73 - 2959735



Side element, with foot, tall version, left-hand, for 73 mm wide U-shaped cover.

---

Side element - UM108-SEPEF/L-A73 - 2906513



Side element with foot, tall design, left, for 73 mm wide U-shaped cover, with PE contact to the DIN rail.

---

Side element - UM108 N-SEFE/L-A73 - 2709367



Side element, with foot, low-profile version, left-hand, for 73 mm wide U-shaped cover.

---

Side element - UM108 N-SEPEF/L-A73 - 2709370



Side element with foot, low-profile design, left, for 73 mm wide U-shaped cover, with PE contact to the DIN rail.

---

Side element - UM108-SE-A60 - 2959748



Side element, without foot, tall version, for 60 mm wide U-shaped cover.

---

## UM108-PROFIL CM - 2959492

### Accessories

Side element - UM108-SE-A73 - 2959751



Side element, without foot, tall version, for 73 mm wide U-shaped cover.

---

Side element - UM108 N-SE-A73 - 2709383



Side element, without foot, low-profile version, for 73 mm wide U-shaped cover.

---

UM108-A/U73-HT CM - 2907680



UM profile cover, tall version, constructional widths 73 mm (internal dimensions 69 mm). Covers of high-temperature resistant PC material. Please include length specifications (in cm) with order no.

---