


SEDECO B-112 INDICATOR LIGHT W/E-5 Lamp (type B)

Unit: mm



DATA	
Material of Body	Phenol Resin + Chrome Plated Brass
Color	Red, Blue, Transparent, Green
Voltage Breakdown	AC 500V / minute
Insulation Resistance	DC 500V 50MOhm or more
Max. Rating	1000mW
Operating Temperature	-20°C ~ +75°C
Terminal	Solder Terminal
Thread	$\Phi 11.0\text{mm} \times L 8.5\text{mm}$ Pitch = 1.0mm
Mounting Hole (Recommended)	$\Phi 11.5\text{mm}$
Lamp	E-5 (type B) 12V/60mA