





Date	Rev.	Description




Model No.	POS.1	POS.2	POS.3
			
1MS3	ON	OFF	ON
Term. Comm.	2-3	OPEN	2-1
SCHEMATIC			

SWITCH FUNCTION



PANEL MOUNTING



SOLDER LUG

SCALE: 3 : 2

TOLERANCE

0.00 mm $\pm$ 0.25mm

0.0 mm $\pm$ 0.40mm

ANGULAR : ϕ 2.54 mm

FILE NAME : 1MSP0178

RATING :

R : 0.4 Volt-Amps(VA) max. @20V max.(AC or DC)

Q : 2Amps @250VAC

5Amps @120 VAC or 28 VDC

SPECIFICATIONS

MECHANICAL LIFE: 40,000 make-and-break cycles.

CONTACT RESISTANCE: 10m Ω max. initial @ 2-4VDC
100mA for both silver and gold plated contacts.

INSULATION RESISTANCE: 1,000M Ω min.

DIELECTRIC STRENGTH: 1,000 V RMS@sea level.

OPERATING TEMPERATURE: -30 ϕ XC to 85 ϕ XC.

MATERIALS

CASE: Dially phthalate (DAP) (UL94v-0).

ACTUATOR: Brass,chrome plated.

BUSHING: Brass,nickel plated.

HOUSING: Stainless Steel.

TERMINAL/CONTACT: Silver or gold plated.

DCC. NO.
A4 DRAWING NO.

MATERIAL		GOLDSUN ELECTRONICS CO., LTD.			
		JAMECO NO.	317308	GOLDSUN NO.	1MS3T6B11M1QE
DRWN: Kiki Chen		Description			Rev.
VERIFY PEOPLE: Ada Zheng , Ivy Lan		MINIATURE TOGGLE SWITCHES			1
		UNIT:	SCALE:	SHEET 1 OF 1	CAS No:
		mm	3:2		ERN No: