




LOC AR	DIST 35	P	F	ZONE	LTR	REVISIONS	
						DESCRIPTION	DATE
					A	REV, REDWN PER ECN 0899	-
					B	REV PER ECN 1456	-
					C	REVSD/ECN CF-1706	07/88
					D	REV ECN CF1770	11-8-88
					E	REV PER ECN CF1807	5-5-89
					F	REV PER ECN BD4386	12-6-90
					G	REV PER EC 0020-1041-93	12/03/93
					H	OBS 1--4 PER EC 0020-933-93	03/16/94
					J	OBSOLETE -13	21 AUG 97
						PER EC 0410-197-96	JGH

- 1 UL RATED 94V-0 THERMOPLASTIC, COLOR: BLACK.
2 PHOSPHOR BRONZE PER QQ-B-750.
3 PLATED WITH .000030 GOLD ON LOCALIZED GOLD PLATE AREA, .000100 - .000200 BRIGHT TIN LEAD ON TERMINATION END, ALL OVER .000050 NICKEL ON ENTIRE CONTACT.
4 POLARIZING FEATURE DOES NOT EXIST ON SAME END AS THE POSN #1 INDICATOR ON 10 AND 14 POSN PRODUCT.



TERMINATED VIEW



DETAIL Z
SCALE 10:1
TYPICAL

OBSOLETE	1.700	1.980	1.750	35	36	1-746290-4
OBSOLETE	2.100	2.380	2.150	43	44	1-746290-3
	3.100	3.380	3.150	63	64	1- ↑ -2
	2.900	3.180	2.950	59	60	1- ↑ -1
	2.400	2.680	2.450	49	50	1- ↑ -0
	1.900	2.180	1.950	39	40	↑ -9
	1.600	1.880	1.650	33	34	↑ -8
	1.400	1.680	1.450	29	30	↑ -7
	1.200	1.480	1.250	25	26	↑ -6
	1.100	1.380	1.150	23	24	↑ -5
	.900	1.180	.950	19	20	↑ -4
	.700	.980	.750	15	16	↑ -3
	.600	.880	.650	13	14	↑ -2
	.400	.680	.450	9	10	↑ 746290-1
	D	C	B	A	NO OF POSN	PART NUMBER

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON :		DR J. PEACHEY 2-19-86	AMP AMP INCORPORATED Harrisburg, Pa. 17105	
2 PL DEC ± .005	3 PL DEC ± .005	CHK JAY SAUDER 2-21-86		
ANGLES ± 5°		APPD JAY SAUDER 2-21-86		
MATERIAL		APPD D. HOFFMAN 2-21-86		
MOLDED PARTS:		PRODUCT SPEC 108-40000	NAME RECEPTACLE KIT, AMP-LATCH NOVO, MIL PLZN, 30 GOLD DUPLEX CONTACTS, W/O STRAIN RLF	
CONTACTS: 2		APPLICATION SPEC 114-40005	SIZE D	F5CM NO 00779
FINISH		WEIGHT -	DRAWING NO 746290	
CONTACTS: 3			SCALE 4:1	SHEET 1 of 1