



A

RELEASED.
DOW 7-19-2012
JUL 20 2012



CUSTOMER DRAWING



CWR-142-XX-0003

1. Dimensions are in inches; dimensions in () are in millimeters.
2. Metric equivalents are given for general information only, and are based upon 1.00 inches equals (25.4) millimeters.
3. Unless otherwise specified, tolerance are ± 0.005 (± 0.13) for three place decimals, and ± 0.01 (± 0.3) for two place decimals.

PLASTIC PARTS - UL94V-0 Thermoplastic (blue, standard)
flame retardant.

CONTACTS - Phosphor bronze, standard;

CONTACT PLATING- .000100 Solder over .000050
Nickel, Std.

TEMPERATURE RATING - 120°C.
CONTACT RATING - 1 Ampere.
DIELECTRIC STRENGTH - Over 500 V.D.C. AT SEA LEVEL.
CONDUCTORS ACCEPTED - 28-30 AWG solid or stranded.

ATTENTION

THIS DRAWING AND ITS ATTACHMENTS, IF ANY, ARE PROPRIETARY TO CW INDUSTRIES AND DESCRIBE DESIGNS THAT ARE CONFIDENTIAL AND MUST NOT BE DISCLOSED UNLESS AUTHORIZED, IN WRITING, BY AN OFFICER OF CW INDUSTRIES.....

CW INDUSTRIES
Southampton, Pa. 18966

TOLERANCES UNLESS OTHERWISE SPECIFIED	
2 Place Decimal $\pm .010$	METRIC
3 Place Decimal $\pm .005$	1 Place Dec. $\pm .25\text{mm}$
Angles $\pm 1'$	2 Place Dec. $\pm .13\text{mm}$

Made for: CW IND.

Drawn by: DGW 7-19-2012

Checked by: G. GULD 7-20-12

Approval: G. GULD 7-20-12

Title:

Title: P.C.B.
CONNECTOR
.145" SOLDER POSTS
W/O/ S/R/ & COVER LIPS

Division:

CONNECTOR

Dwg. No.

CWR-142-XX-0003

MASTER