

Technical datasheet: FT-12T-5.8B1-463

Specifications:

Resonant Frequency	5.8kHz $\pm$ 0.5kHz
Max Resistance (Zr)	500 Ω
Capacitance	10000nF $\pm$ 30%nF

Dimensions:

Type B: (D: Ø12mm, d: Ø9mm. T: 0.12mm, t: 0.05mm)

