



Ty-Rap®

TYB232M

Premium cable tie with stainless steel locking barb to cover the most demanding applications.

T&B Catalog Number:
Description:

TYB232M

Premium, standard cable tie, 203 x 2.4 mm, natural Polyamide 6.6



Technical Information

Type	standard
Material	Polyamide 6.6
Material Locking Barb	316 grade stainless steel
Temperature Range	-40°C to +85°C
Flammability Rating	UL 94 V-2
Colour	natural
Halogen free	yes
Silicone free	yes

Approvals

UL listed	E49405
Germanischer Lloyd approval	yes
Lloyds Register approval	yes

Ordering Information

Length (mm)	203
Width (mm)	2.4
Thickness (mm)	1
Max. Bundle Diameter (mm)	50
Min. Bundle Diameter (mm)	2
Min. Tensile Strength (N)	80
Quantity (pieces)	1000
Packaging Type	workbench box

Storage Conditions

Nylon (Polyamide) is inherently susceptible to environmental conditions. Polyamide 6.6 cable ties are moisturised to optimum performance levels at machine-side and should be stored in cool dry areas out of direct sunlight. Cable ties are packaged in plastic bags to contain moisture and should remain sealed until ready for use.

Tooling

ERG50, WT193A