



**FCRC****Flat Cable Routing Clamp****Specifications:**

- Material: UL94 V-2 Nylon 6/6
- Color: Natural

**Features:**

- Two part design: Cable clamp base and tension-locking cover (sold separately)
- More than one cover can be mounted on base; for strain relief. Double back cable and secure with a second cover
- Base is secured either with a #10 or #12 screw or adhesive




| Base Item No.    |                | A Ref. |      | B Ref. |      | C     |      | Use Cover Item No. |  | D     |      | Bulk Pack Qty. |
|------------------|----------------|--------|------|--------|------|-------|------|--------------------|--|-------|------|----------------|
| Without Adhesive | With Adhesive  | In     | mm   | In     | mm   | In    | mm   |                    |  | In    | mm   |                |
| FCRC-13B-4       | FCRC-13B-4A-RT | 2.040  | 51.7 | 1.620  | 41.2 | 0.500 | 12.7 | FCRC-13C           |  | 2.240 | 56.8 | 100            |
| FCRC-19B-4       | FCRC-19B-4A-RT | 2.720  | 69.1 | 2.310  | 58.7 | 0.500 | 12.7 | FCRC-19C           |  | 2.920 | 74.2 | 100            |
| FCRC-21B-4       | FCRC-21B-4A-RT | 2.980  | 75.7 | 2.550  | 64.8 | 0.500 | 12.7 | FCRC-21C           |  | 3.170 | 80.5 | 100            |
| FCRC-26B-4       | FCRC-26B-4A-RT | 3.660  | 93.0 | 3.240  | 82.3 | 0.500 | 12.7 | FCRC-26C           |  | 3.860 | 98.0 | 100            |
| FCRC-13B-6       | FCRC-13B-6A-RT | 2.040  | 51.7 | 1.620  | 41.2 | 0.750 | 19.1 | FCRC-13C           |  | 2.240 | 56.8 | 100            |
| FCRC-19B-6       | FCRC-19B-6A-RT | 2.720  | 69.1 | 2.310  | 58.7 | 0.750 | 19.1 | FCRC-19C           |  | 2.920 | 74.2 | 100            |
| FCRC-21B-6       | FCRC-21B-6A-RT | 2.980  | 75.7 | 2.550  | 64.8 | 0.750 | 19.1 | FCRC-21C           |  | 3.170 | 80.5 | 100            |
| FCRC-26B-6       | FCRC-26B-6A-RT | 3.660  | 93.0 | 3.240  | 82.3 | 0.750 | 19.1 | FCRC-26C           |  | 3.860 | 98.0 | 100            |

**FCLC / FCLCS****Flat Cable Loop Clip****Specifications:**

- Material: UL94 V-2 Nylon 6/6
- Color: Natural

**Features:**

- Allows for quick positive clamping of flat cable without the need for securing the clip to a board




| Item No. | A Max Cable Width |      | B Ref. |      | C Ref. |     | Bulk Pack Qty. |
|----------|-------------------|------|--------|------|--------|-----|----------------|
|          | In                | mm   | In     | mm   | In     | mm  |                |
| FCLCS    | 1.500             | 38.1 | 2.000  | 50.8 | 0.230  | 5.8 | 500            |
| FCLC     | 2.500             | 63.5 | 3.000  | 76.2 | 0.250  | 6.4 | 500            |

**FCW****Cable Clamp on Adhesive Base****Specifications:**

- Material: Nylon 6/6
- Color: Natural

**Features:**

- Allows for quick positive clamping of flat cable up to 50 conductors wide
- Adhesive base for quick installation
- Latch allows cables to be added and removed





| Item No.   |            | Max # of Conductors | Depth |      | A     |      | B     |      | C Ref. |      | D Ref. |      | Bulk Pack Qty. |
|------------|------------|---------------------|-------|------|-------|------|-------|------|--------|------|--------|------|----------------|
| UL94 V-2   | UL94 V-0   |                     | In    | mm   | In    | mm   | In    | mm   | In     | mm   | In     | mm   |                |
| FCW-29-01  | FCW-29-19  | 30                  | 0.740 | 18.9 | 1.240 | 31.5 | 1.780 | 45.1 | 0.300  | 7.7  | 0.440  | 11.1 | 100            |
| FCW-30-01  | FCW-30-19  | 30                  | 0.750 | 19.1 | 1.240 | 31.5 | 1.790 | 45.5 | 0.350  | 9.0  | 0.520  | 13.1 | 100            |
| FCW-40-01  | FCW-40-19  | 40                  | 0.750 | 19.1 | 1.550 | 39.3 | 2.090 | 53.0 | 0.370  | 9.3  | 0.530  | 13.4 | 100            |
| FCW-50-01  | FCW-50-19  | 50                  | 0.750 | 19.1 | 2.490 | 63.2 | 3.040 | 77.2 | 0.360  | 9.1  | 0.520  | 13.2 | 100            |
| FCW-50H-01 | FCW-50H-19 | 50                  | 0.740 | 18.9 | 2.540 | 64.6 | 3.080 | 78.2 | 0.590  | 15.1 | 0.750  | 19.0 | 100            |

**FCCA / FCCB****Arrowhead Mounted Cable Clamp****Specifications:**

- Material: UL94 V-2 Nylon 6/6
- Color: Natural

**Features:**

- Convenient releasable latch allows easy addition and removal of cables
- Easily mounted into pre-drilled holes

**Figure 1****Figure 2**

| Item No.    | Figure | L     |      | A     |      | B     |      | C     |      | Panel Thickness |           | Depth |      | Bulk Pack Qty. |
|-------------|--------|-------|------|-------|------|-------|------|-------|------|-----------------|-----------|-------|------|----------------|
|             |        | In    | mm   | In    | mm   | In    | mm   | In    | mm   | In              | mm        | In    | mm   |                |
| FCCA-30A-01 | 1      | 2.560 | 65.0 | 2.100 | 52.0 | 0.750 | 19.1 | 1.180 | 30.0 | 0.030 - 0.079   | 0.8 - 2.0 | 0.390 | 10.0 | 100            |
| FCCA-40A-01 | 1      | 2.640 | 67.0 | 5.100 | 53.4 | 0.640 | 16.4 | 1.580 | 40.0 | 0.030 - 0.079   | 0.8 - 2.0 | 0.390 | 10.0 | 100            |
| FCCB-1      | 2      | 3.030 | 77.0 | 2.540 | 64.5 | 0.280 | 7.2  | 2.540 | 64.5 | 0.031 - 0.078   | 0.8 - 2.0 | 0.790 | 20.0 | 100            |
| FCCB-2      | 2      | 3.030 | 77.0 | 2.540 | 64.5 | 0.540 | 13.7 | 2.540 | 64.5 | 0.031 - 0.078   | 0.8 - 2.0 | 0.790 | 20.0 | 100            |