




基板取付穴推奨寸法
RECOMMENDED P.C.BOARD HOLE DIM.



注
NOTE.

1. 材料

MATERIAL

ピン : 0.635×14.2 黄銅、銅下地錫メッキ

PIN: 0.635×14.2 BRASS TIN OVER COPPER PLATING.

ウェハー: ポリアミド, UL94V-0

WAFER: POLYAMIDE, UL94V-0

2. 6極以上に適用

TO BE APPLIED FOR 6 CKT. AND MORE THEN 6 CKT.

3. 5極以下はロック部スリットなし

NO SLIT IS PROVIDED FOR 5 CKT. AND LESS THAN 5 CKT.

4. ELV 及び RoHS 適合品

ELV AND RoHS COMPLIANT

1.35	0.85	47.5 ^{+0.3} _{-0.45}	47.5	22 04 1201	20
↑	↑	45 ^{+0.3} _{-0.45}	45	1191	19
		42.5 ^{+0.3} _{-0.45}	42.5	1181	18
		40 ^{+0.3} _{-0.45}	40	1171	17
		37.5 ^{+0.3} _{-0.45}	37.5	1161	16
		35 ^{+0.3} _{-0.45}	35	1151	15
		32.5 ^{+0.3} _{-0.45}	32.5	1141	14
		30 ^{+0.25} _{-0.4}	30	1131	13
		27.5 ^{+0.25} _{-0.4}	27.5	1121	12
		25 ^{+0.2} _{-0.4}	25	1111	11
		22.5 ^{+0.2} _{-0.4}	22.5	1101	10
		20 ^{+0.15} _{-0.35}	20	1091	9
		17.5 ^{+0.15} _{-0.35}	17.5	1081	8
		15 ^{+0.1} _{-0.3}	15	1071	7
		12.5 ^{+0.1} _{-0.3}	12.5	1061	6
↓	↓	10 ^{+0.5} _{-0.3}	10	1051	5
1.35	0.85	7.5 ^{+0.5} _{-0.3}	7.5	1041	4
1.2	1	5 ^{+0.5} _{-0.3}	5	1031	3
1.2	1	2.5 ^{+0.5} _{-0.3}	2.5	22 04 1021	2
D	E	C	B	ORDER No.	極数 CKT.

MODEL No. : 5045-**A

REVISED EC NO.: J2012-0973 DRAWN: KAWASHIO CHK'D: KASAKAWA APPR.: NUKITA	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 5:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION							
		10 UNDER	± 0.4	DRAWN BY K. KOHAMA	DATE 2000/03/28	TITLE KK 2.5 WAFER ASS'Y WITH LOCK									
		10 OVER 30 UNDER	± 0.45	CHECKED BY T. YAMAGUCHI	DATE 2000/03/30										
		30 OVER	± 0.5	APPROVED BY		DATE	molex								
		ANGULAR ±3 °		MATERIAL NO.		DOCUMENT NO.						SHEET NO.			
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-5045-NA						1 OF 1			
		REV	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												