





PART NUMBER SELECTION TABLES

Feed Through Terminals

PART NUMBER SELECTION TABLES		SAKD 2.5N		SAK 2.5		SAK 4		SAK 6N	
Feed Through Terminals									
		Single Level		Single Level		Single Level		Single Level	
Terminal Block Selection Data									
Available Options		Version							
	Beige PA	0215560000	0268860000	0279660000*	0380460000*	0128360000*	0443660000*	0193260000*	0380560000*
	Beige PA			0218660000		0467460000		0212860000	
	Blue PA	0215580000	0268880000	0279680000*	0380480000*	0128380000*	0443680000*	0193280000*	0380580000*
	Blue PA					0467480000			
	Orange PA			1326360000*		0105060000* 1323660000*			
	Beige KrG			0279620000 0380420000		0128320000 0443620000		0193220000 0380520000	
	Blue KrG			0279670000 0380470000		0128370000 0443670000		0380570000	
	KrS			0279630000		0128330000		0193230000	
	Hexagon socket PA								
	Hexagon socket KrG								
	Blue hexagon socket KrG								
	Hexagon socket KrS								
	KB, 10 PA terminal blocks with marking	401060000	523160000	322560000*	0499460000*	0322660000*	0530460000*	0322760000*	
	KB, 10 PA terminal blocks without marking	401160000	525760000	322860000*	0499560000*	0308860000*	0530360000*	0380960000*	
Dimensions									
Width / Length / Height mm (in.)	for TS 32 	5/44/38 (.197/1.73/1.5)		6/45/40 (.24/1.77/1.57)		6.5/45/44 (.26/1.77/1.73)		8/40/51.5 (.32/1.58/2.07)	
	for TS 35 	5/32.5/43.5 (.197/1.28/1.7)		6/36.5/46.5 (.24/1.44 /1.83)		6.5/40/51.5 (.26/1.57/2.03)		8/45/44 (.32/1.77/1.73)	
Insulation stripping length	mm (in.)	10 (.39)		10 (.39)		12 (.47)		12 (.47)	
Technical Data									
Rated voltage / rated current / wire size	UL	300 V / 20 A / #28...12 AWG		600 V / 20 A / #22...12 AWG		600 V / 30 A / #22...10 AWG		600 V / 40 A / #22...8 AWG	
	CSA	300 V / 20 A / #22...12 AWG		600 V / 25 A / #26...10 AWG		600 V / 36 A / #26...10 AWG		600 V / 47 A / #20...8 AWG	
	VDE	500 V / 26 A / 2.5 mm²		750 V / 26 A / 2.5 mm²		750 V / 34 A / 4 mm²		800 V / 41 A / 6 mm²	
Torque	Nm (lb. in.)	0.8 (7.0)		0.8 (7.0)		1.4 (12.5)		1.8 (16.0)	
Clamping screw	M	2.5		2.5		3		3.5	
Selected Accessory Data†									
End Plate (thickness mm)		Type	Part No.	Type	Part No	Type	Part No.	Type	Part No.
	PA	AP (1.5)	0150960000	AP (1.5) 	0279560000**	AP (1.5)	0117960000	AP (1.5)	0117960000
	Blue PA	AP (1.5)	0150980000	AP (1.5) 	0279580000***	AP (1.5)	0117980000	AP (1.5)	0117980000
	KrG			AP (1.5)	0279520000	AP (1.5)	0117920000	AP (1.5)	0117920000
	Blue KrG			AP (1.5)	0279570000	AP (1.5)	0117970000	AP (1.5)	0117970000
	KrS			AP (1.5)	0279530000	AP (1.5)	0117930000	AP (1.5)	0117930000
Partition (thickness mm)									
	PA	TW (1.5)	0191860000	TW (1.5)	0302860000	TW (1.5)	0130160000	TW (1.5)	0130160000
	Blue PA	TW (1.5)	0191880000	TW (1.5)	0302880000	TW (1.5)	0130180000	TW (1.5)	0130180000
	KrG			TW (2.5)	0302820000	TW (2.5)	0130120000	TW (2.5)	0130120000
	Blue KrG			TW (2.5)	0302870000	TW (2.5)	0130170000		
	KrS			TW (2.5)	0302830000	TW (2.5)	0130130000	TW (2.5)	0130130000
	HP	TW (1.5) 	0307500000	TW (1.0) 	0297100000	TW (1.0) 	0197100000	TW (1.5) 	0197100000
Small Partition									
	TSch 3	0366860000	TSch 1	0319160000	TSch 1	0319160000	TSch 1	0319160000	
Jumpers									
	Q 2	0367800000	Q 2	0337000000	Q 2	0336700000	Q 2	0456700000	
	Q 3	0367900000	Q 3	0337100000	Q 3	0336800000	Q 3	0456800000	
	Q 4	0368000000	Q 4	0337200000	Q 4	0336900000	Q 4	0456900000	
	Q 10	0368100000	Q 10	0368700000	Q 10	0368800000	Q 10	0457000000	
 Connection sleeve Fixing screw Lock washer									
Switchable Jumper Links									
	VL 2					VL 2	0197000000	VL 2	0194700000
	BS					VH 19	0285100000	VH 19	0285100000
	VH					BS M 3 x 25	0292500000	BS M 3 x 25	0292500000
Cover									
	Warning label			AD 3	0297900000	AD 3	0297900000	AD 4	0196600000
	Mounting screw			BSK M 3 x 22	0128900000	BSK M 3 x 22	0128900000	BSK M 3 x 22	0128900000
	Dust cover (1 m)	ADP 1	0485200000	ADP 1	0485200000	ADP 2	0485300000	ADP 2	0485300000
	Holding plate	HP 1	0485560000	HP 1	0485560000	HP 2	0485660000	HP 2	0485660000
Marking Tags		Print							
Note: Part numbers are shown for a single card of pre-printed tags numbered 1-50.	Consecutive horizontal	DEK 5/5	0473460001	DEK 5/6	0468660001	DEK 5/6.5	0468160001	DEK 5/8	1653340001
	Consecutive vertical	DEK 5/5	0473560001	DEK 5/6	0468760001	DEK 5/6.5	0468260001	DEK 5/8	1653350001