


A/C SUPPLY CORD SET SPECIFICATION-HFE1600/U



- 1.UNSHIELDED, 3 CONDUCTORS. 
- 2.PLUG AND CONNECTOR RATING: 15A ; 125Vac.
- 3.TYPE OF CORDAGE: SJT OR SJTO.
- 4.MINIMUM AWG: 14.
- 5.LENGTH OF CORD: 2.0m TYP.
- 6.JACKET COLOR: BLACK OR GRAY.
- 7.JACKET TEMPERATURE RATING: 105°C minimum.
- 8.SAFETY STANDARDS:
CORD SET: UL/CSA
PLUG: UL/CSA LISTED
IEC320 C15 CONNECTOR: UL/CSA APPROVAL
- 9.MARKING:
PLUG: UL/CSA MARK OR UL/CSA FILE NO.
CONNECTOR: UL/CSA MARK OR UL/CSA FILE NO.
VOLTAGE AND CURRENT RATING.
CORD: UL FILE NO., SJT OR SJTO, TEMPERATURE RATING, WIRES AWG.

FIG.1



NOTE:
ROHS COMPLIANCE
REFER TO D-L GROUP
GREEN PROCUREMENT
GUIDELINE : DL-EMS-010_

A	 Ecor178-10	12.OCT.2010			
D	CONTENTS	DATE	ENGR	CHK	APPD
MATERIALS		TITLE	A/C SUPPLY-HFE1600/U		
			CORD SET (FOR USA)		
FINISH		DRAWING No.	1A705-81-07 — 		
		TDK-Lambda			

DWG	K.ROMAN 12/oct/2010	SHEET OF	1 1
ENGR	K.ROMAN 12/oct/2010		
CHK	 12-oct-14.0	SCALE	NONE
APPD	 12-oct-14.0	UNITS	mm
ISSUED			PAGE 1/1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TDK-Lambda:](#)

[HFE/C15U](#)