

40

40 Universal Grip Pliers



40 04 250

- holds round, section and flat material securely
- heavy duty model
- with adjustment screw and release lever
- one-hand operation
- high clamping pressure due to toggle lever action

- plier body: high strength special grade steel
- inserted jaws made from Chrome Vanadium steel, drop forged

Article-No.	EAN-	Head	Handles	Clamping width	
Length mm	Code 4003773-			○ mm □ mm ⬡ mm	g
40 04 180	022190	nickel plated	nickel plated	8 - 35 25 6 - 26	325
250	002710	nickel plated	nickel plated	8 - 35 30 8 - 30	530

41

41 Grip Pliers



41 04 250

Style 0: jaws for round workpieces, with wire cutter


- holds round, section and flat material securely
- heavy duty model
- with adjustment screw and release lever
- one-hand operation
- high clamping pressure due to toggle lever action

- plier body: high strength special grade steel
- inserted jaws made from Chrome Vanadium steel, drop forged



41 14 250

Style 1: jaws with double prism for round, section and flat material



Example 41 14 250



41 24 225

Style 2: straight jaws for flat material



41 34 165

Style 3: Long-Nose Grip Plier, narrow, long jaws

Article-No.	EAN-	Style	Head	Handles	Clamping width	
Length mm	Code 4003773-				○ mm □ mm ⬡ mm	g
41 04 180	002741	0	nickel plated	nickel plated	8 - 30 20 6 - 24	360
250	002758				8 - 40 20 8 - 30	530
300	022183				10 - 65 30 10 - 34	930
41 14 250	023470	1	nickel plated	nickel plated	36 36 13 - 36	560
41 24 225	023487	2	nickel plated	nickel plated	42 16 0 - 24	505
41 34 165	047858	3	nickel plated	nickel plated	6.5 - 30 10 6 - 24	200