

**Part Number: 94234-1004**

CONN FOR LAMP TIN PL 4 CKT

Image not available

Status:	OBsolete
Replacement:	Contact Molex
Series:	94234
Category:	PCB Headers

Series image - Reference only

Product Environmental Compliance

EU RoHS: ELV and RoHS Compliant

China RoHS:

REACH SVHC: Contains SVHC: No

Low-Halogen Status: Not Reviewed

Part Detail**General**

Status	Obsolete
Category	PCB Headers
Series	94234
Application	Board-to-Board, Power
Product Name	Lamp Header

Physical

Breakaway	No
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black
Glow-Wire Compliant	No
Material - Metal	Copper-Nickel-Silicon
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Number of Rows	1
Orientation	Vertical
PC Tail Length	2.40mm
PCB Locator	No
PCB Thickness - Recommended	1.00mm
Packaging Type	Bag
Pitch - Mating Interface	5.20mm
Pitch - Termination Interface	2.30mm, 2.90mm
Plating min - Mating	3.048µm
Plating min - Termination	3.048µm
Polarized to Mating Part	Yes
Polarized to PCB	No
Shrouded	No
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40°C to +130°C
Termination Interface: Style	Through Hole

Electrical

(Please review the Product Specification for specific details.)

Current - Maximum per Contact	Contact Molex
Voltage - Maximum	250V

Material Info

UPC	800754330466
-----	--------------

Reference - Drawing Numbers

Sales Drawing	SD-94234-003
---------------	--------------

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

**Previously Available Application
Tooling**
[Check our list of old tooling that used to be
available for this part](#)