

PNEUMATIC CRIMPER

PC 24 - 14 B

BENCH-CRIMPER

TRAPEZOID CRIMPING

SIDE AND FRONT INSERTION

UNIVERSAL - DIE

RANGE 24-14 AWG (0.25-2.50 MM²)

LENGTH: 7.9 INCHES (200 MM)

WEIGHT: 35.2 OUNCES (1000 G)

PRESSURE: 58 PSI (4 BAR)

PC 24 - 14 H

HAND-CRIMPER

TRAPEZOID CRIMPING

SIDE AND FRONT INSERTION

UNIVERSAL - DIE

RANGE 24-14 AWG (0.25-2.50 MM²)

LENGTH: 7.9 INCHES (200 MM)

WEIGHT: 35.2 OUNCES (1000 G)

PRESSURE: 58 PSI (4 BAR)



PC 24 - 14 H
CLOSE UP VIEW

PC 12 - 8 B

BENCH-CRIMPER

TRAPEZOID CRIMPING

SIDE ENTRY

RANGE 12-8 AWG (4-10 MM²)

LENGTH: 7.9 INCHES (200 MM)

WEIGHT: 15.1 OUNCES (430 G)

PRESSURE: 58 PSI (4 BAR)

PC 12 - 8 H

HAND-CRIMPER

TRAPEZOID CRIMPING

SIDE ENTRY

RANGE 12-8 AWG (4-10 MM²)

LENGTH: 7.9 INCHES (200 MM)

WEIGHT: 15.1 OUNCES (430 G)

PRESSURE: 58 PSI (4 BAR)


ACCESSORY EQUIPMENT:

PC - 1

BALANCER

PC - 2

MAGNETIC TOOL HOLDER



AMERICAN ELECTRICAL, INC.
1811 HUGUENOT ROAD
SUITE NO. 205
MIDLOTHIAN, VA 23113

TELEPHONE: (804) 379 - 2899

FAX: (804) 379 - 8935

DOC9703R0