

## Cable sleeve - KDT 2/7 - 3063442

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Small, slotted cable sleeves suitable for two conductors with a diameter of 2 x 7 mm.

### Product Description

Slotted sleeves for accommodation of two conductors with a 2 x 7 mm diameter, can be used in KEL sealing frames: KEL 16/4, KEL 16/8, KEL 24/4, KEL 24/5, KEL 24/7, KEL 24/10. The sleeves also serve as strain relief devices as per DIN EN 50262 when installed.

**RoHS**

### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
Weight per Piece (excluding packing)	7.320 g
Custom tariff number	40169300
Country of origin	Germany

### Technical data

#### Dimensions

External cable diameter	7 mm
-------------------------	------

#### Ambient conditions

Degree of protection	IP54
Ambient temperature (operation)	-20 °C ... 80 °C

#### General

Product description	Slotted sleeves for accommodation of two conductors with a 2 x 7 mm diameter, can be used in KEL sealing frames: KEL 16/4, KEL 16/8, KEL 24/4, KEL 24/5, KEL 24/7, KEL 24/10. The sleeves also serve as strain relief devices as per DIN EN 50262 when installed.
No. of conductors	2
Material	Elastomer

## Cable sleeve - KDT 2/7 - 3063442

### Technical data

#### General

Flammability rating according to UL 94	V0
Color	gray

#### Standards and Regulations

Flammability rating according to UL 94	V0
--	----

### Classifications

#### eCl@ss

eCl@ss 4.0	27081002
eCl@ss 4.1	27081002
eCl@ss 5.0	27081002
eCl@ss 5.1	27081002
eCl@ss 6.0	27081002
eCl@ss 7.0	27081002
eCl@ss 8.0	27069216
eCl@ss 9.0	27144421

#### ETIM

ETIM 2.0	EC000451
ETIM 3.0	EC000879
ETIM 4.0	EC000879
ETIM 5.0	EC000879

#### UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	39121708
UNSPSC 11	39121708
UNSPSC 12.01	39121708
UNSPSC 13.2	39121708