

PRODUCT SPECIFICATION

Brand	C.K
Product Range	Hammers
Catalogue number	5701, 5702, 5703, 4229, 4203, 4232, 4219, 4218, 4234, 4204, 4208, 4227A & 4225
Date	01/04/2009

Range Description

A complete range of construction hammers.

Features

Single piece forged claw hammers (5701)

- Single piece forged steel shaft for maximum strength and performance
- Balanced weight design with energy saving claw geometry
- Shock absorbing contoured grip system for comfort and control

Fibreglass shafted claw hammers (5702)

- Strong fibreglass shaft for strength and performance
- Balanced weight design with energy saving claw geometry
- Shock absorbing contoured grip system for comfort and control

Single piece forged club hammer (5703)

- Single piece forged steel shaft for maximum strength and performance
- Shock absorbing contoured grip system for comfort and control



Steel claw hammer (4229)

- Drop forged high carbon steel head, hardened and tempered – strong and durable
- Steel shafted
- Highly coloured rubber grip – for visibility and comfort
- Coated and lacquered for protection

**Cross pein hammer (4203)**

- Drop forged high carbon steel head, hardened and tempered – strong and durable

**Brick hammer (4232)**

- Drop forged high carbon steel head, hardened and tempered – strong and durable
- Tough cutting edge with accurately ground and beveled face
- Chrome plated steel shaft
- Contoured comfort grip

**Club hammer (4219)**

- Drop forged high carbon steel head, hardened and tempered – strong and durable
- Ground and polished striking faces
- Genuine hickory handle



Club hammer (4219A)

- Drop forged high carbon steel head, hardened and tempered – strong and durable
- Ground and polished striking face
- Head black lacquered for protection
- Ash handle
- Head secured by a ring wedge

**Sledge hammer (4218)**

- Drop forged high carbon steel head, hardened and tempered – strong and durable
- Ground and polished striking face
- Vibration damping fiberglass shaft with shock absorbing rubber collar

**Mortar pick (4234)**

- Drop forged high carbon steel head, hardened and tempered – strong and durable
- Chrome plated steel shaft
- Contoured comfort grip
- Chisel and point combination ends

**Joiners hammer (4204)**

- Drop forged high carbon steel head, hardened and tempered – strong and durable
- Hickory shaft for strength

**Engineers hammer (4208)**

- Drop forged high carbon steel head, hardened and tempered – strong and durable
- Hickory shaft for strength



Engineers hammer (4227)

- Traditional German pattern
- Drop forged high carbon steel head, hardened and tempered – strong and durable
- Ash shaft for strength

**Engineers hammer (4225)**

- Traditional French pattern
- Drop forged high carbon steel head, hardened and tempered – strong and durable
- Ash shaft for strength



Item Number	Item Description	EAN No	Commodity code	Carton Qty
357001	Forged one piece hammer 16oz	5051073570018	82052000	6
357002	Forged one piece hammer 20oz	5051073570025	82052000	6
357003	Fibreglass shaft hammer 16oz	5051073570032	82052000	6
357004	Fibreglass shaft hammer 20oz	5051073570049	82052000	6
357005	Forged single piece club hammer 3lb	5051073570056	82052000	2
T4229 08	Steel claw hammer – high visibility 8oz Yellow	5013969051612	82052000	6
T4229 16	Steel claw hammer – high visibility 16oz Orange	5013969960907	82052000	6
T4229 20	Steel claw hammer – high visibility 20oz Green	5013969119404	82052000	6
T4203	Cross pein pin hammer	5013969522105	82052000	3
T4232 16	Brick hammer 16oz	5013969746907	82052000	4
T4232 20	Brick hammer 20oz	5013969306804	82052000	4
T4219 40	Club hammer 21/2lb	5013969524406	82052000	2
T4219 64	Club hammer 4lb	5013969524505	82052000	2
T4219A 10	Club hammer 1000g	5013969972825	82052000	6
T4219A 15	Club hammer 1500g	5013969972832	82052000	6
T421808	Sledge hammer 8lb	5013969068955	82052000	2
T421812	Sledge hammer 12lb	5013969068962	82052000	2
T4234	Mortar pick – chisel and point	5013969929300	82052000	6
T4204 06	Joiners Hammer 6oz	5013969522204	82052000	3
T4204 08	Joiners Hammer 8oz	5013969522303	82052000	3
T4204 10	Joiners Hammer 10oz	5013969522402	82052000	3
T4208H 08	Engineers Hammer 1/2lb	5013969523201	82052000	3
T4208H 16	Engineers Hammer 1lb	5013969523409	82052000	3
T4208H 24	Engineers Hammer 11/2lb	5013969523508	82052000	3

T4208H 32	Engineers Hammer 2lb	5013969523607	82052000	3
T4227A 0100	Engineers Hammer 100g	5013969970425	82052000	12
T4227A 0200	Engineers Hammer 200g	5013969970432	82052000	12
T4227A 0300	Engineers Hammer 300g	5013969970499	82052000	12
T4227A 0500	Engineers Hammer 500g	5013969970456	82052000	12
T4227A 1000	Engineers Hammer 1000g	5013969970487	82052000	6
356001	Engineers Hammer 200g	5051073560019	82052000	12
356002	Engineers Hammer 300g	5051073560026	82052000	12

Technical product information	
Standards compliance	Where applicable, the hammers are produced generally in accordance with BS879
User health and safety information	Users and bystanders are advised to wear safety goggles
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	The hammers are guaranteed for life against imperfect materials or workmanship Damage caused through inappropriate use is not covered
Country of origin	4219A, 4225 & 4227A – Italy 4234 – Japan All others – Taiwan

Dimensional details

	Product only				Product on primary packaging			
Item	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
357001	130	35	340	760	130	35	340	763
357002	135	35	363	870	135	35	363	873
357003	130	35	335	763	130	35	335	766
357004	135	35	335	837	135	35	335	840
357005	100	40	280	1605	100	40	280	1608
T4229 08	100	18	280	392	100	18	280	394
T4229 16	130	35	325	744	130	35	325	746
T4229 20	130	35	330	821	130	35	325	823
T4203	100	20	320	215	100	20	320	215
T4232 16	175	30	290	742	175	30	290	742
T4232 20	175	30	290	876	175	30	290	876
T4219 40	90	40	245	1296	90	40	245	1296
T4219 64	105	45	245	1196	105	45	245	1197
T4219A 10	93	37	260	1052	93	37	260	1052
T4219A 15	107	42	280	1635	107	42	280	1635
T421808	155	55	855	4412	155	55	855	4412
T421812	190	60	860	6227	190	60	860	6227
T4234	260	23	285	657	260	23	285	657
T4204 06	100	22	275	294	100	22	275	294
T4204 08	105	22	295	337	105	22	295	337
T4204 10	115	23	295	429	115	23	295	429
T4208H 08	84	20	300	348	84	20	300	348
T4208H 16	103	25	355	666	103	25	355	666
T4208H 24	120	25	390	886	120	25	390	886
T4208H 32	130	28	380	1098	130	28	380	1098
T4227A 0100	80	15	260	163	80	15	260	163
T4227A 0200	90	18	280	271	90	18	280	271
T4227A 0300	103	21	305	379	103	21	305	379
T4227A 0500	115	26	320	648	115	26	320	648
T4227A 1000	135	33	365	1200	135	33	365	1200
356001	140	15	265	247	140	15	265	247
356002	90	20	300	343	90	20	300	343
	Shelf box (secondary packaging)				Euro Pallet data			

					Wi x Hi	
Item	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
357001	148	390	95	4815		
357002	160	410	95	5468		
357003	148	390	95	4790		
357004	160	410	100	5255		
357005	105	375	47	3308		
T4229 08	120	335	95	2511		
T4229 16	145	380	95	4678		
T4229 20	145	380	95	5140		
T4203	105	375	50	742		
T4232 16	185	330	75	3148		
T4232 20	185	330	75	3528		
T4219 40	105	310	55	2702		
T4219 64	115	345	60	4110		
T4219A 10	125	330	110	6427		
T4219A 15	140	360	120	9981		
T421808	180	930	70	9301		
T421812	220	930	70	12919		
T4234	290	330	100	4233		
T4204 06	115	345	60	1002		
T4204 08	125	360	60	1148		
T4204 10	125	360	60	1424		
T4208H 08	100	360	60	1153		
T4208H 16	125	420	70	2175		
T4208H 24	145	460	85	2877		
T4208H 32	145	460	85	3514		
T4227A 0100	120	300	95	2047		
T4227A 0200	120	330	100	3276		
T4227A 0300	145	350	115	4684		
T4227A 0500	170	380	130	7958		
T4227A 1000	115	430	145	7347		
356001	145	345	115	3123		
356002	145	345	115	4275		

Packaging waste details

	Primary Packaging				Secondary packaging			
Item	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
357001			3	Tag	12	Bag	201	Box
357002			3	Tag	12	Bag	201	Box
357003			3	Tag	12	Bag	201	Box
357004			3	Tag	12	Bag	231	Box
357005			3	Tag	12	Bag	108	Box
T4229 08			1	Tag	1	Bag	147	Box
T4229 16			1	Tag	1	Bag	202	Box
T4229 20			1	Tag	1	Bag	202	Box
T4203					1	Bag	102	Box
T4232 16					6	Bag	152	Box
T4232 20					6	Bag	152	Box
T4219 40					1	Bag	110	Box
T4219 64					1	Bag	116	Box
T4219A 10							115	Box
T4219A 15							171	Box
T421808					8	Bag	469	Box
T421812					8	Bag	469	Box
T4234					1	Bag	291	Box
T4204 06					1	Bag	117	Box
T4204 08					1	Bag	134	Box
T4204 10					1	Bag	134	Box
T4208H 08					1	Bag	106	Box
T4208H 16					1	Bag	174	Box
T4208H 24					1	Bag	216	Box
T4208H 32					2	Bag	216	Box
T4227A 0100							91	Box
T4227A 0200							91	Box
T4227A 0300							136	Box
T4227A 0500							182	Box
T4227A 1000							147	Box
356001							159	Box
356002							159	Box