


Sortie coudee



Part number: DM537435000NC

DM 53743-5000 NC	Ct coax femelle sortie coudee	1.00	1.75	2.32	3.20	RG 178 BU KX 21 A
Ref contact	Designation	$\phi A^{\pm 0.10}_0$	$\phi B^{\pm 0.05}_0$	$\phi C^{\pm 0.10}_0$	$\phi D^{\pm 0.10}_0$	Ref cable

rev	ecn no	dr	date
B	-	MAS	2000/08/16
C	LS05-0026	MPE	2005/07/08
D	LS05-0084	MPE	2005/09/28
E	LS06-0095	LGO	2006/06/29
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com		surface ISO 1302	tolerance std ISO 406 ISO 1101	projection A3	mm
TOLERANCES UNLESS OTHERWISE SPECIFIED		ANGULAR	LINEAR	size	Scale
Dr	BOUITIER	1990/09/07	0.X	±0.1	5
Eng	PESSON	1990/09/07	0.XX	±0.1	
Chr	LEGARE	1990/09/07	0.XX* ±2*	±0.1	
Appr	LEGARE	1990/09/07	Product family	D-SUB	Spec ref -
FCI		CONTACT COAX FEMELLE SORTIE COUDEE		cat no	C-8639-505
-		-		Rev.	E
-		-		CUSTOMER sheet 1 of 1	

REV F - 2006-04-17

PDM: Rev:E

STATUS: Released

Printed: Oct 01, 2010