






[illegible]

SCALE 4:1

4032.2	24	46.2[1.82]	51.7[2.04]	2-106527-4
3717.6	22	42[1.65]	47.5[1.87]	2-106527-2
3403.1	20	37.8[1.49]	43.3[1.7]	2-106527-0
3088.6	18	33.6[1.32]	39.1[1.54]	1-106527-8
2774	16	29.4[1.16]	34.9[1.37]	1-106527-6
2459.5	14	25.2[0.99]	30.7[1.21]	1-106527-4
2145	12	21[0.83]	26.5[1.04]	1-106527-2
1830.5	10	16.8[0.66]	22.3[0.88]	1-106527-0
1515.9	8	12.6[0.5]	18.1[0.71]	106527-8
1201.4	6	8.4[0.33]	13.9[0.55]	106527-6
886.9	4	4.2[0.17]	9.7[0.38]	106527-4
575.1	2	0[0]	5.5[0.22]	106527-2
VOLUME mm ³	NO OF POSITIONS	B	A±0.2[.01]	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER 27JUN2007 CHK C CASH 27JUN2007		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.21 (0.1) 1 PLC ±0.21 (0.1) 2 PLC ±0.13 (0.005) 3 PLC ± 4 PLC ± ANGLES ±°0°30'		NAME AMP-DUAC(TM) RECEPTACLE HAVING, 2 TO 24 POSITION, -	
		PRODUCT SPEC - APPLICATION SPEC -		SIZE A1	
MATERIAL 		FINISH -		CAGE CODE 100779	
		WEIGHT -		DRAWING NO. C106527	
		CUSTOMER DRAWING		SCALE 4:1 SHEET 1 OF 1 REV E2	

METRIC