

PRODUCT FAMILIES

Pin Headers and Sockets

Clips and Insulators

Banana Plugs and Jacks

Grabbers, Probes and Spade Terminals

Plunger Clips

Test Probes

Spade Terminals

Test Leads and Patch Cords

Coaxial Cable Assemblies

DMM Kits

Plunger Clips

Plunger Clip

TOOL

SEARCH TOOLS

MUELLER OR DISTRIBUTOR STOCK SEARCH

PART #

SEARCH

TOOL

CROSS COMPETITOR PART #

Choose a Brand

PART #

SEARCH

TOOL

MeterMate® DMM ACCESSORY SELECTOR

Select Meter Make

Select a Make First

TOOL

BUILD A PCB HEADER OR SOCKET

OVER 10,000 IN STOCK!

GO

ISO 9001:2000

Model # BU-00201-*/BU-00202-*/BU-00203-*

- Material: Cap & Body: glass filled nylon; Spring: stainless steel; Contact: beryllium copper; insulated to a single contact point
- Length: 1.75" (44mm) (BU-00201-*); 2.50" (63mm) (BU-00202-*); 3.50" (88mm) (BU-00203-*)
- *Std. Colors: -0 Black, -2 Red
- Rating: 1000 Volts, 10 Amps

Safety Plunger Clip Adapter



Model # BU-00207-*

- Material: Cap & Body: nylon; Spring: stainless steel; Contact: beryllium copper
- Length: 2.23" (56.64mm)
- *Std. Colors: -0 Black, -2 Red
- Rating: 1000 Volts, 15 Amps

Mini-Micro Plunger Clip



Model # BU-00208-*

- Material: Cap & Body: tough, durable nylon; Spring: stainless steel compression coil; Contact: gold-plated beryllium copper
- Length: 1.75" (44mm)
- *Std Colors: -0 Black, -2 Red
- Rating: 600 Volts, 3 Amps

Right Angle Insulated Plunger Hook Clip



Model # BU-20431-*

- Compatible with all shrouded, unshrouded, or retractable 0.16" (4mm) banana plugs
- Material: Housing: nylon. Contact: nickel-plated beryllium copper
- Length: 4.60" (116.84mm); the hook extends 0.41" (10mm) when fully depressed
- *Std Colors: -0 Black, -2 Red, -4 Yellow, -6 Blue
- Rating: 1000V, 15 Amps, IEC 1010 Compliant

Right Angle Insulated Plunger Clamp Clip



Model # BU-20432-*/BU-20433-*

- Compatible with all shrouded, unshrouded, or retractable 0.16" (4mm) banana plugs
- Material: Housing: nylon. Contact: nickel-plated beryllium copper
- Length: 5.50" (139.7mm) (BU-20432-*); 7.50" (190.5mm) (BU-20433-*)
- *Std Colors: -0 Black, -2 Red, -4 Yellow, -6 Blue
- Rating: 1000V, 1 Amps, IEC 1010 Compliant

Right Angle Insulated Plunger Jaw Clip



Model # BU-20434-*

- Compatible with all shrouded, unshrouded, or retractable 0.16" (4mm) banana plugs
- Material: Housing: nylon. Contact: nickel-plated steel
- Length: 5.26" (133.6mm); the steel jaws extend 0.48" (12mm) and open to 1" (25mm)
- *Std Colors: -0 Black, -2 Red, -4 Yellow, -6 Blue
- Rating: 1000V, 15 Amps, IEC 1010 Compliant