

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [503149-3000](#)
Status: **Active**
Overview: [CLIK-Mate™ Wire-to-Board Connectors](#)
Description: 1.50mm Pitch CLIK-Mate™ Wire-to-Board Housing, Dual Row, Positive Lock, 30 Circuits

Documents:
[3D Model](#)
[Drawing \(PDF\)](#)
[Application Specification AS-503149-001 \(PDF\)](#)
[Packaging Specification SPK-503149-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E29179

General

Product Family Crimp Housings
Series [503149](#)
Application Signal, Wire-to-Board
Overview [CLIK-Mate™ Wire-to-Board Connectors](#)
Product Name CLIK-Mate™
UPC 884982019621

Physical

Circuits (maximum) 30
Color - Resin Beige
Gender Plug
Glow-Wire Compliant No
Keying to Mating Part Yes
Lock to Mating Part Yes
Net Weight 900.000/mg
Number of Rows 2
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 1.50mm
Polarized to Mating Part Yes
Stackable No
Temperature Range - Operating -25°C to +85°C


Electrical

Current - Maximum per Contact 2A

Material Info

Reference - Drawing Numbers

Application Specification AS-503149-001
Packaging Specification SPK-503149-001
Product Specification RPS-503148-001, RPS-503148-003, RPS-503148-005, RPS-503154-001, RPS-503154-002, RPS-503154-003, RPS-503154-004, RPS-503154-005, RPS-503154-007, RPS-503154-008, RPS-503154-009, RPS-503154-010, RPS-503154-011, RPS-503354-001
Sales Drawing SD-503149-001



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[503149Series](#)

Mates With
[503154](#) PCB Receptacle

Use With
[502579](#) Crimp Terminal