




QUALITY ENCLOSURES

[Home](#)[Company Info](#)[Product Catalog](#)[Distributors](#)[Representatives](#)[What's New](#)[Search](#)[Contact](#)[Get A Quote](#)

NEMA 1, 2, 4, 4X, 12, 13
Boxes (Sheet Metal)
**SN-Series NEMA
Sheet Metal
Boxes**

[Click on Image for Larger View](#)

These sheet metal boxes meet NEMA 1, 2, 4, 4X, 12, 13, and IP65 ratings and can be mounted without need to remove cover and expose internal components.

Design Features

- Made from durable 14 ga. steel (0.078" thick).
- Smooth continuous welded seams.
- External mounting brackets allow the box to be mounted on a wall or panel without having to remove the cover and exposing internal components to the environment.
- Hinged cover clamps to the base with stainless steel brackets and steel screws for a watertight seal.
- Weld nuts for inner panel mounting.
- Bonding studs for grounding are provided on base and door.
- Easily machined and modified to your particular requirements.
- Internal panel and hardware included.
- Tested and listed to UL-508 Type 4x requirements (UL File #E194432)
- Finish: Smooth gray powder coat

NEMA 4 SHEET METAL BOX WITH MOUNTING BRACKET

Catalog Number	Drawings	External Dimensions (Base)			External Dimensions (Overall)			Wall Mounting Dimensions		Internal Panel Dimensions		Wgt. Lbs.
		A	B	C	D	E	F	G	H	I	J	
SN-3700	PDF DXF	6.00"	4.00"	3.00"	7.50"	7.07"	3.25"	6.31"	2.00"	4.90"	2.90"	4
SN-3701	PDF DXF	8.00"	6.00"	3.50"	9.50"	9.07"	3.75"	8.31"	4.00"	6.90"	4.90"	7
SN-3702	PDF DXF	6.00"	6.00"	4.00"	7.50"	7.07"	4.25"	6.31"	4.00"	4.90"	4.90"	6
SN-3703	PDF DXF	12.00"	10.00"	5.00"	13.50"	13.07"	5.25"	12.31"	8.00"	10.90"	8.90"	16
SN-3704	PDF DXF	10.00"	8.00"	6.00"	11.50"	11.07"	6.25"	10.31"	6.00"	8.90"	6.90"	12
SN-3705	PDF DXF	12.00"	12.00"	6.00"	13.50"	13.07"	6.25"	12.31"	10.00"	10.90"	10.90"	19
SN-3706	PDF DXF	14.00"	12.00"	6.00"	15.50"	15.07"	6.25"	14.31"	10.00"	12.90"	10.90"	21
SN-3707	PDF DXF	16.00"	14.00"	6.00"	17.50"	17.07"	6.25"	16.31"	12.00"	14.90"	12.90"	27
SN-3708	PDF DXF	14.00"	12.00"	8.00"	15.50"	15.07"	8.25"	14.31"	10.00"	12.90"	10.90"	24
SN-3709	PDF DXF	16.00"	14.00"	10.00"	17.50"	17.07"	10.25"	16.31"	12.00"	14.90"	12.90"	33

[DXF](#) Autocad DXF Specifications File
(Requires CAD software such as AutoCAD)

[PDF](#) Adobe PDF Specifications File



[Download PDF Viewer](#)

Get A Quote

[Home](#) | [Company Info](#) | [Online Catalog](#) | [Check Stock](#) | [Distributor/Price](#)












[Reps](#) | [New](#) | [Search](#) | [Contact](#) | [Privacy Policy](#)

BUD INDUSTRIES INC.

P.O. Box 998
Willoughby, Ohio 44094

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF
BUD INDUSTRIES INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT
THE WRITTEN PERMISSION OF BUD INDUSTRIES INC. IS PROHIBITED.

DATE: NO.	SEE TABLE
ISSUE	REVISIONS



PART NUMBER	A	B	C	D	E	F	G	H	J	K	# BRACKETS/SCREWS/LATCHES
SN-3700	6.00	4.00	3.00	6.75	2.00	3.00	6.31	4.31	3.25	5.00	3
SN-3701	8.00	6.00	3.50	8.75	4.00	5.00	8.31	6.31	3.75	7.00	3
SN-3702	6.00	6.00	4.00	6.75	4.00	5.00	6.31	6.31	4.25	5.00	3
SN-3703	12.00	10.00	5.00	12.75	8.00	9.00	12.31	10.31	5.25	11.00	6
SN-3704	10.00	8.00	6.00	10.75	6.00	7.00	10.31	8.31	6.25	9.00	4
SN-3705	12.00	12.00	6.00	12.75	10.00	11.00	12.31	12.31	6.25	11.00	6
SN-3706	14.00	12.00	6.00	14.75	10.00	11.00	14.31	12.31	6.25	13.00	6
SN-3707	16.00	14.00	6.00	16.75	12.00	13.00	16.31	14.31	6.25	15.00	7
SN-3708	14.00	12.00	8.00	14.75	10.00	11.00	14.31	12.31	8.25	13.00	6
SN-3709	16.00	14.00	10.00	16.75	12.00	13.00	16.31	14.31	10.25	15.00	7

PARTS LIST			
P-1 BUSH BETWEEN HOLES CONTACT P-2 BUSH BETWEEN DRUMMED HOLES P-3 BUSH BETWEEN A BUSH SURFACE P-4 BUSH BETWEEN ATTACHED SURFACES UNLESS OTHERWISE SPECIFIED		C-1 CHAMFERED DRUMMED C-2 NOT CHAMFERED SPECIFIED	BUD INDUSTRIES INC. NEMA HINGED ENCLOSURE
MATERIAL: AS NOTED FINISH: SEE SPEC. DO NOT SCALE DRAWINGS	APPROVAL: DP DATE: 1/13/06 CHECKED: REVISIONS:	D: SEE TABLE	