


LST-120-07-G-D

LST-112-07-S-D



.100" (2,54mm) SOCKET/TERMINAL LST, HLST SERIES

SPECIFICATIONS

For complete specifications see www.samtec.com?LST or www.samtec.com?HLST

LST

Insulator Material:

LST: Black
Glass Filled Polyester

Terminal Material:

Phosphor Bronze

Contact Material:

Phosphor Bronze

Plating:

Au or Sn over 50µ" (1,27µm) Ni

Operating Temp Range:

-55°C to +125°C with Gold

-55°C to +105°C with Tin

Insertion Depth:

(3,68 mm) .145" to (6,35 mm) .250"

Insertion Force:

(Single contact only)

6oz (1,67N) avg

Withdrawal Force:

(Single contact only)

4oz (1,11N) avg

Cycles:

100 with 10µ" (0,25µm) Au

RoHS Compliant:

Yes

Lead-Free Solderable:

Wave Only

HLST

Same as LST except:

Insulator Material:

Liquid Crystal Polymer

(Socket Black, Header Natural)

Processing:

Max Processing Temp:

230°C for 60 seconds, or

260°C for 20 seconds 3x

Lead-Free Solderable:

Yes



Mates with:
LST, HLST



CURRENT RATING

AMBIENT TEMP	5 Contacts
20°C	6.0A
40°C	5.3A
60°C	4.2A
80°C	3.0A

Note: Some lengths, styles and options are non-standard, non-returnable.

Hermaphroditic self-mating combination header/socket system


One part number for both socket and terminal

(2,54mm) .100" pitch

Polarized

(0,64mm) .025" square post

APPLICATION



Locking feature increases unmating force and provides audible "click" when properly mated

TYPE STRIP

1

NO. PINS PER ROW

07

PLATING OPTION

D

LST
= Standard

02 thru 30

HLST
= High Temperature

-G

= 10µ" (0,25µm) Gold on contact area, Gold flash on balance

-S

= 30µ" (0,76µm) Gold on contact area, Matte Tin on tail

-F

= Gold flash on contact area, Matte Tin on tail


-T

= Matte Tin

Also Available


Right Angle

Call Samtec.




Elevated

Call Samtec.







Surface Mount

Call Samtec.



Edge Mount

Call Samtec.



Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM