

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0679290341
Status: Contact Molex
Description: 0.50mm (.020") Pitch FPC Connector, Surface Mount, Right Angle, ZIF, Bottom Contact Type, 34 Circuits, Lead Free



Series

image - Reference only

Documents:

[3D Model](#) [Product Specification PS-67929-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family FFC/FPC Connectors
Series 67929
Product Name N/A

Physical

Circuits (Loaded) 34
Contact Position Bottom
Durability (mating cycles max) 20
Entry Angle 90° Angle
Mated Height 2.00mm (.079")
Material - Metal Phosphor Bronze
Material - Plating Mating Tin-Bismuth
Material - Plating Termination Tin-Bismuth
Number of Rows 1
Orientation Right Angle
PCB Locator No
PCB Retention Yes
Packaging Type Embossed Tape on Reel
Pitch - Mating Interface 0.50mm (.020")
Plating min - Mating 1.270µm (50µ")
Plating min - Termination 1.270µm (50µ")
Polarized to PCB Yes
Stackable No
Surface Mount Compatible (SMC) N/A
Temperature Range - Operating -20°C to +85°C
Termination Interface: Style Surface Mount
Wire/Cable Type FFC/FPC

Electrical

Current - Maximum per Contact 0.5A
Voltage - Maximum 50V

Solder Process Data

Lead-free Process Capability Reflow Capable (SMT only)
Process Temperature max. C 240

Material Info

Reference - Drawing Numbers

Product Specification PS-67929-001
Sales Drawing SD-67929-001

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series
67929Series