


# Manhattan™ Cordsets

## 300 V 3-Conductor Cordage

### Rubber



**SJ, SV**  
**UL 62**  
**CSA C22.2 No. 49**

**Operating Temperature**  
• -30°C to +90°C

**Conductor Color Coding**  
• Black, white, green

**Materials**  
• Stranded bare copper conductors  
• Rubber insulation  
• Black chlorinated polyethylene jacket

**Availability**  
250 ft (76.2 m)  
(Minimums may apply)

3-Conductor Cords (Unshielded)

| Part No. | Wire Size |                 | Stranding |           | Insulation Thickness |      | Jacket Thickness |      | Cable Dimension |      |
|----------|-----------|-----------------|-----------|-----------|----------------------|------|------------------|------|-----------------|------|
|          | AWG       | mm <sup>2</sup> | AWG       | mm        | Inch                 | mm   | Inch             | mm   | Inch            | mm   |
| Type SJ  |           |                 |           |           |                      |      |                  |      |                 |      |
| 1952/3   | 18        | 0.81            | 16/30     | 16 x 0.25 | 0.032                | 0.81 | 0.034            | 0.86 | 0.309           | 7.85 |
| 1953/3   | 16        | 1.32            | 26/30     | 26 x 0.25 | 0.032                | 0.81 | 0.034            | 0.86 | 0.340           | 8.64 |
| Type SV  |           |                 |           |           |                      |      |                  |      |                 |      |
| 1951/3   | 18        | 0.82            | 41/34     | 41 x 0.16 | 0.017                | 0.43 | 0.036            | 0.91 | 0.256           | 6.50 |