



## Combination pliers, 2628G

**ISO:** 5746

**DIN:** 5746


**Finish:** black oxidised, anti-corrosion treated.

**Material:** Chrome-Vanadium steel. With Ergo handles in two-material combination. Thermoplastic surface on tough polypropylene which gives a superior grip.

**Shape:** an "open" joint, in which the distance from the joint centre to the cutting edges is reduced, results in greater leverage and increased cutting capacity. Equipped with return spring with on/off function. Round shaped jaws give improved accessibility in confined spaces.

**Application:** the edges specially designed to cut harder material such as piano wire and spring steel wire. Gripping surfaces particularly suited for gripping round and flat material.

**Cutting capacity:** piano wire.



|  | <br>731415+ |  | <b>A</b><br>mm | <b>B</b><br>mm | <b>C</b><br>mm | <b>D</b><br>mm | <b>E</b><br>mm | <b>F</b><br>mm | <b>G</b><br>mm |  |  |
|-----------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| 2628 G-160                                                                        | 0042999                                                                                      | 5                                                                                 | 160            | 33             | 23             | 10.5           | 3.5            | 10.5           | 12             | 1.8                                                                                 | 190                                                                                 |
| 2628 G-180                                                                        | 0042678                                                                                      | 5                                                                                 | 180            | 36             | 25             | 11.0           | 4.0            | 11.0           | 14             | 2.0                                                                                 | 240                                                                                 |
| 2628 G-200                                                                        | 0103539                                                                                      | 5                                                                                 | 200            | 39             | 27             | 12.0           | 4.5            | 12.0           | 16             | 2.5                                                                                 | 300                                                                                 |
| 2628 G-160IP                                                                      | 0055357                                                                                      | 5                                                                                 | 160            | 33             | 23             | 10.5           | 3.5            | 10.5           | 12             | 1.8                                                                                 | 190                                                                                 |
| 2628 G-180IP                                                                      | 0044030                                                                                      | 5                                                                                 | 180            | 36             | 25             | 11.0           | 4.0            | 11.0           | 14             | 2.0                                                                                 | 240                                                                                 |
| 2628G-200IP                                                                       | 0101085                                                                                      | 5                                                                                 | 200            | 39             | 27             | 12.0           | 4.5            | 12.0           | 16             | 2.5                                                                                 | 300                                                                                 |