

Heavy Duty Terminal Blocks

0987 RZ Series - Deadfront Type

600 Volts AC/DC (UL/CSA)




0987 RZ TC 07

Specifications:

- Base, Thermoplastic, 125°C, Flammability - UL 94 V-O
- Connector, Copper Alloy, Nickel Plated (TC Tubular Clamp)
- Current Rating up to **50 Amps**
- Wire Range
 - (1) #8 - #24 sol/str
 - (2) 12 str
 - (2) 14 str
 - (1) 12 str and (1) 14 str
- .475" Centerline Spacing
- IP20 Touchproof Protection
- UL Recognized File No. XCFR2.E47811
- CSA Certified File No. LR19766
- **CE** - 1000 Volts
- RoHS Compliant

Catalog #	# of poles	Dimensions	
		A	B
0987 RZ TC 02	2	0.95	N/A
0987 RZ TC 03	3	1.43	0.48
0987 RZ TC 04	4	1.90	0.95
0987 RZ TC 05	5	2.38	1.43
0987 RZ TC 06	6	2.85	1.90
0987 RZ TC 07	7	3.33	2.38
0987 RZ TC 08	8	3.80	2.85
0987 RZ TC 09	9	4.28	3.33
0987 RZ TC 10	10	4.75	3.80
0987 RZ TC 11	11	5.23	4.28
0987 RZ TC 12	12	5.70	4.75

mm = dim X 25.4



For electronic drawings or 2D/3D CAD data, submit request at www.marathonsp.com/drawings.html