

Our new 2012 models have arrived!

Home > Phones & Home Office > Multifunction Printers > KX-FLB811

All-in-One Flatbed Laser Fax

Model number: KX-FLB811

★★★★★ This product has not yet been rated. Be the first to WRITE A REVIEW!

Print this | Share this

All-in-One Flatbed Laser Fax with Document Sorter

Available at your favorite retailer



enlarge



Overview	Tech Specifications	Reviews	FAQs	Accessories	Operating Manuals	Warranty & Care Plans
GENERAL FUNCTION						
Multifunction Operation		Yes, with PC Print, Scan and copy				
2-Line, 16-character LCD Display		Yes				
Print Method		Laser				
Document Management		Separate fax documents from prints and copies.				
USB/Parallel/PC Interface ¹		USB only				
Flatbed		Yes				
Automatic Document Feeder (pages)		Yes, up to 40 sheets				
Paper Tray Capacity		up to 250 sheets (LTR/LGL)				
Optical Character Recognition (OCR) Software		Yes				
PRINTER FUNCTION						
High Speed (pages per minute)		up to 18				
Print Resolution		600 dpi				
Compatible Operating Systems		Windows®98/Me/2000/XP				
Paper size		LTR/LGL/A4				
Plain Paper		Yes				
COPIER FUNCTION						
Multi-Copy		up to 99				
Reduction Copy		to 50%, 5% steps				
Enlargement Copy		to 200%, 5% steps				
FAX FUNCTION						
Modem Speed (Kbps)		up to 33.6				
Resolution		photo/super fine/fine/standard				
64-Level Photo Resolution		Yes				
Dual Access		Yes				
Error Correction Mode		Yes				
Quick Scan		Yes				
Broadcasting		Yes, 20 Locations				
Navigator Key		Yes				
Distinctive Ring Detection ²		Yes				
Extension Line Transfer		Yes				
Help Function		Yes				
OTHER FUNCTIONS						
TEL/TAD/FAX Switching		Yes				
Out of Paper Reception ³		up to 170 pages				
Electronic Volume Control		Yes				
One-Touch Stations		7 keys, 14 entries				
Speed Dial Stations		up to 314				
Monitor Speaker		Yes				
Answering Machine Interface		Yes				
Fax Advantage Program		Overnight Exchange1-year Warranty				
Caller ID ⁴		Compatible				
1. USB and Parallel (IEEE 1284) cable not included.						
2. Requires subscription to fee-based phone company service.						
3. Actual number of pages depends upon the contents of the pages and the resolution. Page capacity based upon ITU-T No. 1 test chart at standard resolution.						
4. Requires subscription to fee-based, caller ID phone company service(s).						

You may also like



High Speed Multifunction Office Machine
(1 Reviews)
Suggested Retail Price: \$419.95
KX-MB3020
LEARN MORE



24PPM 4-in-1 Monochrome Laser MFP
Suggested Retail Price: \$189.95
KX-MB2030
LEARN MORE

Need assistance with your order?

Email click here

Call 1-800-405-0652
Mon-Fri 8:00 AM - 9:00 PM EST
Sat-Sun 12:00 PM - 5:00 PM EST

Live Chat click here

Recently Viewed Products



13-Watt Energy Efficient Compact Fluorescent Light Bulb, Spiral-Shape

EFD13E28



Multi-Function Laser Fax, PC-Printer, Copier and Scanner

★★★★★2 Reviews

KX-FLM651



VIERA® 32" Class X34 Series LCD HDTV (31.5" Diag.)

★★★★★1 Reviews

TC-32LX34

View more