

RESETTABLE CIRCUIT  
BREAKER

PILOT LIGHT

482.60 mm  
[19.000 in]

43.64 mm  
[1.718 in]

165.10 mm  
[6.500 in]

38.10 mm TYP  
[1.500 in]

ASSEMBLY - VIEW FROM FRONT

19.05 mm  
[0.750 in]

444.50 mm  
[17.500 in]

5.08 mm  
[0.200 in]

67.58 mm  
[2.661 in]

A↑

↑A

6' FOOT  
POWER CORD  
(NEMA 5-15P)

ASSEMBLY - VIEW FROM BOTTOM

10.31 mm  
[0.406 in]

461.98 mm  
[18.188 in]


5.97 mm  
[0.235 in]

31.70 mm  
[1.248 in]


127.00 mm  
[5.000 in]

SECTION A-A

R3.18 mm  
[0.125 in]



ISOMETRIC VIEW



ASSEMBLY - VIEW FROM SIDE

#### 1582T8A1BK

Finish - Front - Black Painted Steel

Back - Black Painted Steel

Rated - 125 VAC, 60 Hz, 15 Amps

Approvals - CSA Certified Standards C22.2 (No. 21-95, 42-99)

- UL Recognized Standard UL1363

#### Colours & Cord Length

1582T8A1BK - Black w/ 6' Foot Power Cord (NEMA 5-15P)

1582T8A1 - ASA 61 Grey w/ 6' Foot Power Cord (NEMA 5-15P)

1582T8B1BK - Black w/ 15' Foot Power Cord (NEMA 5-15P)

1582T8B1 - ASA 61 Grey w/ 15' Foot Power Cord (NEMA 5-15P)



**HAMMOND  
MANUFACTURING™**

**1582T8A1BK**

[www.hammondmfg.com](http://www.hammondmfg.com)