






100 SQ.
[1.039] TYP.




DUAL SNAP FEATURE
CENTERED ON PLUG
ALIGNMENT FEATURE TO
MATCH FEATURE ON PLUG

AUXILIARY VIEW
SCALE 1:1

SINGLE SNAP FEATURE
TO THE RIGHT OF ALIGNMENT
FEATURE, 2 & 3 CIRCUIT PARTS

NOTES:

1. MATERIAL: SEE TABLE
2. FINISHES: SEE TABLE
3. PRODUCT SPECIFICATION: PPS.98.002
4. INCH DIMS ARE SHOWN IN BRACKETS [XXX].
5. "XX" REFERS TO QTY. OF CIRCUITS.
6. ASSEMBLY IS ROHS COMPLIANT.
7. REPLACES DWG. SD-39980-0402.



NUMBER OF CIRCUITS "XX"	DIM. "A"	DIM. "B"	DIM. "C" .013	MATERIAL NO. TIN (STD)	MATERIAL NO. GOLD OPTION
02	10.77 [4.24]	5.08 [2.00]	N/A	39980-0402	39981-0402
03	15.85 [6.24]	10.16 [4.00]	5.08 [2.00]	39980-0403	39981-0403
04	20.93 [8.24]	15.24 [6.00]	5.08 [2.00]	39980-0404	39981-0404
05	26.01 [10.24]	20.32 [8.00]	5.08 [2.00]	39980-0405	39981-0405
06	31.09 [12.24]	25.40 [10.00]	10.16 [4.00]	39980-0406	39981-0406
07	36.17 [14.24]	30.48 [12.00]	10.16 [4.00]	39980-0407	39981-0407
08	41.25 [16.24]	35.56 [14.00]	15.24 [6.00]	39980-0408	39981-0408
09	46.33 [18.24]	40.64 [16.00]	15.24 [6.00]	39980-0409	39981-0409
10	51.41 [20.24]	45.72 [18.00]	20.32 [8.00]	39980-0410	39981-0410
11	56.49 [22.24]	50.80 [2.00]	20.32 [8.00]	39980-0411	39981-0411
12	61.57 [24.24]	55.88 [2.200]	25.40 [1.000]	39980-0412	39981-0412
13	66.65 [26.24]	60.96 [2.400]	25.40 [1.000]	39980-0413	39981-0413
14	71.73 [28.24]	66.04 [2.600]	30.48 [1.200]	39980-0414	39981-0414
15	76.81 [30.24]	71.12 [2.800]	30.48 [1.200]	39980-0415	39981-0415
16	81.89 [32.24]	76.20 [3.000]	35.56 [1.400]	39980-0416	39981-0416
17	86.97 [34.24]	81.28 [3.200]	35.56 [1.400]	39980-0417	39981-0417
18	92.05 [36.24]	86.36 [3.400]	40.64 [1.600]	39980-0418	39981-0418
19	97.13 [38.24]	91.44 [3.600]	40.64 [1.600]	39980-0419	39981-0419
20	102.21 [40.24]	96.52 [3.800]	45.72 [1.800]	39980-0420	39981-0420
21	107.29 [42.24]	101.60 [4.000]	45.72 [1.800]	39980-0421	39981-0421
22	112.37 [44.24]	106.68 [4.200]	50.80 [2.000]	39980-0422	39981-0422
23	117.45 [46.24]	111.76 [4.400]	50.80 [2.000]	39980-0423	39981-0423
24	122.53 [48.24]	116.84 [4.600]	55.88 [2.200]	39980-0424	39981-0424

WIDTH WAS .62/IS .60 EC NO: WNA2009-0464 ID: WNA2009-0464 CHKD: RDOERSS APPR: RDOERSS 2009/02/03 2009/02/05 2009/02/09	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± .005 2 PLACES ± 0.13 ± .01 1 PLACE ± 0.3 ± --- ANGULAR ± 2 °	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	DIMENSION STYLE MM/IN	SCALE 3:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION	TITLE 5.08/200 SINGLE ROW EUROSTYLE HEADER ASSEMBLY	MATERIAL NO. SD-39980-006	SHEET NO. 1 OF 1