

### Example 1

## STEINEL®

### Heat Blowers

Powerful heat blowers with lightweight ergonomic design, soft grip handle and quiet operation for convenient long term use.

Interchangeable temperature keys lock-in specific output ranges. Available with choice of 1 to 5 color coded keys for the right temperature every time. Maintenance-free factory sealed motor and high output turbine fan deliver up to 23 CFM.

Adjustable quick-lock stand stores keys. Tool removes easily for hand held operation. Long-life reinforced element with plug-in feature takes only seconds to change.

Made in E.U.   



34750

Each key defines a specific temperature range.

| Part# | Model    | Description                  | Temperature Range | Voltage @60 Hz | Output Watts | Shipping Weight | Weight (Net) lbs. |
|-------|----------|------------------------------|-------------------|----------------|--------------|-----------------|-------------------|
| 34750 | HB1750   | Heat Blower w/ all Five Keys | 200° - 1200°F     | 120 VAC        | 1750         | 3.4             | 2.4               |
| 34751 | HB1750 B | Heat Blower w/ Blue Key      | 200° - 300°F      | 120 VAC        | 1750         | 3.4             | 2.4               |
| 34752 | HB1750 G | Heat Blower w/ Gray Key      | 300° - 500°F      | 120 VAC        | 1750         | 3.4             | 2.4               |
| 34753 | HB1750 Y | Heat Blower w/ Yellow Key    | 500° - 750°F      | 120 VAC        | 1750         | 3.4             | 2.4               |
| 34754 | HB1750 O | Heat Blower w/ Orange Key    | 750° - 1000°F     | 120 VAC        | 1750         | 3.4             | 2.4               |
| 34755 | HB1750 R | Heat Blower w/ Red Key       | 1000° - 1200°F    | 120 VAC        | 1750         | 3.4             | 2.4               |

### Blower Accessories



| Part # | Description              | Application                    |
|--------|--------------------------|--------------------------------|
| 07695  | 1/4" / 7mm Reducer       | Pinpoint heat                  |
| 07725  | 8" / 200mm Spreader      | Films & Packaging              |
| 07705  | Large Reflector          | Shrink tubing up to 50 mm dia. |
| 07715  | Small Reflector          | Shrink tubing up to 20 mm dia. |
| 07681  | Set of Five Keys (1 ea.) | Temp Range 200°F - 1200°F      |

### Example 2

## STEINEL®

### HB1750 Series

### Heat Blowers

Powerful heat blowers with interchangeable temperature keys feature plug-in element and adjustable stand. Available with 1 to 5 keys to lock-in a specific temperature range within 200°F - 1200°F.

23 CFM, 1750 watts, 120 VAC, 60Hz, double insulated for safe operation

- No. 34750 Blower w/ all 5 Keys
- No. 34751 Blower w/ 200 - 300°F Blue Key
- No. 34752 Blower w/ 300 - 500°F Gray Key
- No. 34753 Blower w/ 500 - 750°F Yellow Key
- No. 34754 Blower w/ 750 - 1000°F Orange Key
- No. 34755 Blower w/ 1000 - 1200°F Red Key

- No. 07695 7mm Reducer Nozzle
- No. 07725 200mm Spreader Nozzle
- No. 07705 Large Reflector Nozzle
- No. 07715 Small Reflector Nozzle

