



(2.54 mm) .100"

TSSH-115-01-L-D



TSSH-120-01-L-DH



TSSH SERIES

SHROUDED .025" SQ POST HEADERS

Board Mates:

SSW, SSQ, SSM

Cable Mates:

SMSD

Important Note:

Important Note:
This Series will only mate
with SSW, SSQ, SSM &
SMSD Series

SPECIFICATIONS

Insulator Material:
Black Liquid Crystal
Polymer

Terminal Material:
Phosphor Bronze

Phosphor Bronze Plating:

Au or Sn over
50 μ" (1.27 μm) Ni

Operating Temp

-55 °C to +105 °C with Tin

-55 °C to +125 °C with Gold
RoHS Compliant:
Yes

PROCESSING

Lead-Free Solderable:

Yes

SMT Lead Coplanarity (-DV):
(2.12) (2.12) (2.12)

(0.10 mm) .004" max (05-10)

(0.15 mm) .006" max (15-20)*
(0.20 mm) .008" max (25-36)*

SMT Lead Coplanarity (-DH):

(0.15 mm) .0006" max*

*(.004" stencil solution

may be available)

RECOGNITIONS



APPLICATIONS




ALSO AVAILABLE
(MOQ Required)

- Other platings

Note:

Some lengths, styles and options are non-standard, non-returnable.



Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.TOBY.CO.UK

All parts within this catalog are built to Samtec's specifications.

Customer specific requirements must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.