






- NOTES:
- 1) STANDARD PACK QUANTITY: 1000.
 - 2) ALL PRIMARY DIMENSIONS IN mm, ALL SECONDARY DIMENSIONS IN [INCHES].
 - 3) MAX. CABLE DIAMETER = 4.5mm.
 - 4) MAXIMUM SCREW SIZES:
M3 x 0.6, No. 6 SCREW UNC, No.6 SCREW UNF.

INFORMATION CONTAINED IN THIS DOCUMENT IS CONFIDENTIAL TO RICHCO INTERNATIONAL Co. Ltd. AND MAY NOT BE DISCLOSED OR REPRODUCED IN WHOLE OR PART WITHOUT THEIR WRITTEN CONSENT



METRIC GENERAL TOLERANCES ± 0.25
ARE PRIMARY UNLESS OTHERWISE STATED
1 DECIMAL PLACE $\pm$
2 DECIMAL PLACES $\pm$
ANGULAR $\pm 1^\circ$

IMPERIAL GENERAL TOLERANCES ± 0.010
ARE FOR REFERENCE UNLESS OTHERWISE
1 DECIMAL PLACE $\pm$
2 DECIMAL PLACES $\pm$
ANGULAR $\pm 1^\circ$

MATERIAL: NYLON 6/6 (RMS-48)				COLOUR: GREY	
DESCRIPTION: STRAIN RELIEF CABLE CLAMP				PART No: SRCC-1	
DRG No: 04-081		NPR REF:			SIZE A4
DRN NJB	DATE 23/07/04	CHKD OW	DATE 23/07/04		
SCALE NTS		SHEET No 1 OF 1			