

Shielded Hoods, Top Entry

DTK/DTPK I-Series

TECHNICAL SPECIFICATIONS

Material:

Plastic Hood: Polyamid – UL-recognized
Metal Hood: Steel, Zinc plated metal insert

Operating Temperature: -30°C to 110°C

Cable Entry: Top and Side**

Thumbscrews: UNC 4-40 (standard)
M2,5 or M3,0 on request

Cable Diameter: Up to 13,0 mm


Colour: Black (standard)
Other colours on request

Accessories: See page 25-26

Features:

- Available in sizes 9-15-25-37-50**
- Suitable for IDC connectors
- Quick-Snap locking system
- Crimping method ensures a 360° shielding
- The 50-way hood is available in IPI-version or Slide-Lock version
(IPI: Intelligent Peripheral Interface)

**** 50-way hood also available in Side-entry version.
Please contact us for more information.**



Size DTK/DTPK	Dim A	Dim B	Dim C
9-way	35,0	54,0	19,0
15-way	43,0	54,0	19,0
25-way	54,0	53,0	18,0
37-way	74,0	54,0	19,0
50-way **	-	-	-

Ordering information:**Hoods in Single-Pack:**

9-way	6260-0120-xx
15-way	6260-0121-xx
25-way	6260-0122-xx
37-way	6260-0123-xx
50-way	On request

Hoods in Bulk-Pack:

9-way	6261-0120-xx
15-way	6261-0121-xx
25-way	6261-0122-xx
37-way	6261-0123-xx
50-way	On request

Code for correct ferrule:

Cable O.D	Size	Order Code xx	Suits Hood size
Up to 5,1 mm	R5,3	-10	9-15-25-37
4,3–6,9 mm	R7,1	-12	9-15-25-37
6,1–8,8 mm	R9,0	-14	9-15-25-37
8,0–10,3 mm	R10,5	-15	9-15-25-37
9,5–11,5 mm	R11,7	-16	9-15-25-37-50
11,0–13,1 mm	R13,3	-18	50