



#### FEATURES:

- Breakout quickly converts a BNC cable to flying leads
- Lead ends can be attached to terminal strips or customized
- BNC connector is molded directly to the wire for pull strength durability and dust and moisture resistance
- BNC center contact is gold plated Beryllium Copper for corrosion resistance, low contact resistance and long insertion life
- Black lead is connected to BNC shell, red lead to BNC center contact

#### MATERIALS:

BNC: Nickel plated brass

Center Contact: Gold plated Beryllium Copper

Wire: 20 AWG, PVC

Marking: "POMONA 4969" or "POMONA 4970"

#### RATINGS:

Operating Voltage: 500 VRMS

Operating Temperature: +55°C (+131°F) Max.

#### ORDERING INFORMATION: Model 4969 or 4970

BNC breakouts with banana plugs, spade lugs, alligators and Minigrabber test clips are also available

\*Custom lengths are available, contact Pomona Technical support: 800-241-2060 (Technicalsupport@pomonatest.com)

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Sales: 800-490-2361 Fax: 888-403-3360 Technical Assistance: 800-241-2060  
For "Where to Buy" information, visit the Pomona web site at [www.pomonaelectronics.com](http://www.pomonaelectronics.com)