



- Durable nylon cable clamps

|                 |                             |
|-----------------|-----------------------------|
| Part Number:    | CCH56-S10-C                 |
| Product Family: | Fixed Diameter Cable Clamps |
| Product Line:   | Screw/Rivet Applied         |

|                         |           |
|-------------------------|-----------|
| RoHS Compliancy Status: | Compliant |
|-------------------------|-----------|

|                   |                                       |
|-------------------|---------------------------------------|
| Part Description: | Heavy Duty Fixed Diameter Cable Clamp |
|-------------------|---------------------------------------|

|               |                 |
|---------------|-----------------|
| Product Type: | Mounting Device |
|---------------|-----------------|

|           |           |
|-----------|-----------|
| Material: | Nylon 6.6 |
|-----------|-----------|

|        |         |
|--------|---------|
| Color: | Natural |
|--------|---------|

|                |         |
|----------------|---------|
| UL Recognized: | E136577 |
|----------------|---------|

|                 |     |
|-----------------|-----|
| Diameter (In.): | .20 |
|-----------------|-----|

|                |     |
|----------------|-----|
| Diameter (mm): | 5.1 |
|----------------|-----|

|              |     |
|--------------|-----|
| Width (In.): | .50 |
|--------------|-----|

|             |      |
|-------------|------|
| Width (mm): | 12.7 |
|-------------|------|

|                             |                |
|-----------------------------|----------------|
| Bundle Offset (mm):         | 15.5           |
| Bundle Offset (In.):        | .61            |
| Environment:                | Indoors        |
| Flammability Rating:        | UL94 V-2       |
| Hole Diameter (In.):        | .20            |
| Hole Diameter (mm):         | 5.1            |
| Max. Bundle Diameter (In.): | .56            |
| Max. Bundle Diameter (mm):  | 14.2           |
| Metric Screw Size:          | M5             |
| Mounting Method:            | #10 (M5) Screw |
| Screw Size:                 | #10 (M5)       |
| Std. Pkg. UOM:              | PK             |
| Type Of Application:        | Heavy Duty     |
| UOM:                        | PC             |
| Std. Pkg. Qty.:             | 100            |
| Min. Order Qty.:            | 100            |