

VFFC Series

Heat Shrink Tubing

pro-POWER

RoHS
Compliant



Features:

- 2:1 shrink ratio
- Low shrink temperature reduces installation time and the risk of damage to temperature-sensitive components
- Very flexible; doesn't easily wrinkle when bent
- Hot stamps extremely well
- Higher temperature rating, better thermal stability, and higher resistance to physical abuse than non-crosslinked materials
- Free of polybrominated biphenyls (PBBs) and polybrominated biphenyl oxides and ethers (PBBOs and PBBEs), which are classified as environmentally hazardous substances
- Polyolefin tubing

Applications:

Cost-effective choice for many commercial and military applications; electrically insulates and protects in-line components, disconnect terminals, and splices. Bundles wires for very flexible light-duty harnesses. Strain-relieves electrical wire connections for commercial applications. Identifies or colour-codes wires, cables, terminals, and components.

Specifications:

Installation:

Minimum Shrink Temperature	: 70°C (158°F)
Minimum Full Recovery Temperature	: 90°C (194°F)
Operating Temperature Range	: -55°C to 135°C (-67°F to 275°F)

Part Number Table

Description	Size (Inches)	Colour	Inside Diameter		Recovered Wall Thickness* After Heating	Part Number
			Expanded as Supplied	Maximum Recovered After Heating		
Heatshrink, 1.6mm, Black, 1.2m	1/16	Black	1.85 ±0.2 (0.073 ±0.008)	0.8 (0.031)	0.43 ±0.08 (0.017 ±0.003)	VFFC-1/16-0-STK
Heatshrink, 2.4mm, Black, 1.2m	3/32		2.79 ±0.2 (0.110 ±0.008)	1.2 (0.046)	0.51 ±0.08 (0.020 ±0.003)	VFFC-3/32-0-STK
Heatshrink, 3.2mm, Black, 1.2m	1/8		3.43 ±0.2 (0.135 ±0.008)	1.6 (0.062)		VFFC-1/8-0-STK
Heatshrink, 4.8mm, Black, 1.2m	3/16		5.21 ±0.3 (0.205 ±0.010)	2.4 (0.093)		VFFC-3/16-0-STK

Dimensions : Millimetres (Inches)

VFFC Series

Heat Shrink Tubing

pro-POWER

Part Number Table

Description	Size (Inches)	Colour	Inside Diameter		Recovered Wall Thickness* After Heating	Part Number
			Expanded as Supplied	Maximum Recovered After Heating		
Heatshrink, 6.4mm, Black, 1.2m	1/4		7.11 $\pm$ 0.3 (0.280 $\pm$ 0.010)	3.2 (0.125)	0.64 $\pm$ 0.08 (0.025 $\pm$ 0.003)	VFFC-1/4-0-STK
Heatshrink, 9.5mm, Black, 1.2m	3/8		10.16 $\pm$ 0.4 (0.400 $\pm$ 0.015)	4.8 (0.187)		VFFC-3/8-0-STK
Heatshrink, 12.7mm, Black, 1.2m	1/2		13.72 $\pm$ 0.4 (0.540 $\pm$ 0.015)	6.4 (0.250)		VFFC-1/2-0-STK
Heatshrink, 19mm, Black, 1.2m	3/4		20.45 $\pm$ 0.4 (0.805 $\pm$ 0.015)	9.5 (0.375)	0.76 $\pm$ 0.08 (0.030 $\pm$ 0.003)	VFFC-3/4-0-STK
Heatshrink, 25.4mm, Black, 1.2m	1		25.53 $\pm$ 0.4 (1.055 $\pm$ 0.015)	12.7 (0.500)	0.89 $\pm$ 0.12 (0.035 $\pm$ 0.005)	VFFC-1-0-STK
Heatshrink, 1.6mm, Black, 5m	1/16		1.85 $\pm$ 0.2 (0.073 $\pm$ 0.008)	0.8 (0.031)	0.43 $\pm$ 0.08 (0.017 $\pm$ 0.003)	VFFC-1/16-0
Heatshrink, 3.2mm, Black, 5m	1/8		3.43 $\pm$ 0.2 (0.135 $\pm$ 0.008)	1.6 (0.062)	0.51 $\pm$ 0.08 (0.020 $\pm$ 0.003)	VFFC-1/8-0
Heatshrink, 4.8mm, Black, 5m	3/16	Black	5.21 $\pm$ 0.3 (0.205 $\pm$ 0.010)	2.4 (0.093)		VFFC-3/16-0
Heatshrink, 6.4mm, Black, 5m	1/4		7.11 $\pm$ 0.3 (0.280 $\pm$ 0.010)	3.2 (0.125)	0.64 $\pm$ 0.08 (0.025 $\pm$ 0.003)	VFFC-1/4-0
Heatshrink, 9.5mm, Black, 5m	3/8		10.16 $\pm$ 0.4 (0.400 $\pm$ 0.015)	4.8 (0.187)	0.64 $\pm$ 0.08 (0.025 $\pm$ 0.003)	VFFC-3/8-0
Heatshrink, 12.7mm, Black, 5m	1/2		13.72 $\pm$ 0.4 (0.540 $\pm$ 0.015)	6.4 (0.250)		VFFC-1/2-0
Heatshrink, 19mm, Black, 5m	3/4		20.45 $\pm$ 0.4 (0.805 $\pm$ 0.015)	9.5 (0.375)	0.76 $\pm$ 0.08 (0.030 $\pm$ 0.003)	VFFC-3/4-0
Heatshrink, 25.4mm, Black, 5m	1		25.53 $\pm$ 0.4 (1.055 $\pm$ 0.015)	12.7 (0.500)	0.89 $\pm$ 0.12 (0.035 $\pm$ 0.005)	VFFC-1-0
Heatshrink, 2.4mm, Black, 5m	3/32		2.79 $\pm$ 0.2 (0.110 $\pm$ 0.008)	1.2 (0.046)	0.51 $\pm$ 0.08 (0.020 $\pm$ 0.003)	VFFC-3/32-0

Note: Wall thickness will be less if tubing recovery is restricted during shrinkage.

Dimensions : Millimetres (Inches)

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of the Group. © Premier Farnell plc 2012.

www.element14.com
www.farnell.com
www.newark.com
www.cpc.co.uk

pro-POWER